

AMG EP 2010**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Efficient machine and facility operation calls for fail-safe and maintenance-friendly control voltage distribution that can be installed in a time and space-saving manner.

With the new maxGUARD system, the terminal blocks (previously installed separately) for distributing potential to the outputs of the electronic load monitors become an integral part of a 24 V DC control voltage distribution system.

The innovative combination of load monitoring and potential distribution saves time during installation, increases safety against failure and reduces the amount of space required on the terminal rail by 50%.

General ordering data

| Version | Fastening element |
|------------|----------------------------|
| Order No. | 2495380000 |
| Type | AMG EP 2010 |
| GTIN (EAN) | 4050118505306 |
| Qty. | 30 pc(s). |

AMG EP 2010

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 96.5 mm | Depth (inches) | 3.799 inch |
| Height | 125 mm | Height (inches) | 4.921 inch |
| Width | 8 mm | Width (inches) | 0.315 inch |
| Net weight | 32.599 g | | |

Temperatures

| | | | |
|---------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -25 °C...70 °C |
|---------------------|----------------|-----------------------|----------------|

General data

| | | | |
|-------------------|-----|-------------------|------|
| Conformal coating | Yes | Protection degree | IP20 |
|-------------------|-----|-------------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000886 | ETIM 7.0 | EC000886 |
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ECLASS 9.0 | 27-14-11-33 | ECLASS 9.1 | 27-14-11-33 |
| ECLASS 10.0 | 27-14-11-33 | ECLASS 11.0 | 27-14-11-33 |
| ECLASS 12.0 | 27-14-11-33 | ECLASS 13.0 | 27-25-03-01 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | Declaration of Conformity UK Conformity Assessed |
| Engineering Data | CAD data – STEP |
| User Documentation | Manual_maxGUARD |
| Catalogues | Catalogues in PDF-format |

AMG EP 2010**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****W-Series**

W
Series

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WEW 35/1 V0 GF SW | Version |
| Order No. | 1478990000 | End bracket, Wemid, black, Rail: TS 35, when screwed in |
| GTIN (EAN) | 4050118286892 | |
| Qty. | 50 pc(s). | |