

PRO COM DISPLAY 7S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller's plug-in communication modules enable individual components to exchange relevant data with the cloud. This lays the foundation for targeted process optimization using condition monitoring and remote controllability - factors that play a decisive role in increasing efficiency, quality, process stability and availability can contribute. The communication modules are designed according to IP20 protected, can be operated without tools and can be flexibly adapted to different customisable communication protocols.

General ordering data

Communication module	
Version	Communication module
Order No.	2466960000
Type	PRO COM DISPLAY 7S
GTIN (EAN)	4050118481808
Qty.	1 pc(s).

PRO COM DISPLAY 7S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	33.6 mm	Depth (inches)	1.323 inch
Height	74.4 mm	Height (inches)	2.929 inch
Width	34 mm	Width (inches)	1.339 inch
Net weight	80 g		

Temperatures

Operating temperature	-25 °C...70 °C
-----------------------	----------------

General data

MTTF	According to Standard	SN 29500
	Operating time (hours), min.	2,505,000 h
	Ambient temperature	40 °C
	Duty cycle	100 %
Protection degree	IP20	

Electrical safety (applied standards)

Protection against dangerous shock currents	Acc. to VDE0106-101	Safety transformers for switch-mode power supplies	According to EN 61558-2-16
---	---------------------	--	----------------------------

Approbations

Certificate no. (cULus)	E258476	Certificate no. (cULusEX)	E470829
Institute (cULus)	CULUS	Institute (cULusEX)	CULUSEX

Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-04-07-92
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-24-26-08	ECLASS 13.0	27-24-26-08

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Lead monoxide 1317-36-8
SCIP	d62541f7-8058-4336-b693-7303c8b40800

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E258476
Certificate no. (cULusEX)	E470829

PRO COM DISPLAY 7S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	Manual PRO COM DISPLAY 7S Instruction sheet
Catalogues	Catalogues in PDF-format

PRO COM DISPLAY 7S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

