


EF 20 55 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

General ordering data

Version	Exhaust filter, IP55, grey
Order No.	2557110000
Type	EF 20 55 GY
GTIN (EAN)	4050118567748
Qty.	1 pc(s).

EF 20 55 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	31 mm	Depth (inches)	1.22 inch
Height	145 mm	Height (inches)	5.709 inch
Width	145 mm	Width (inches)	5.709 inch
Net weight	120 g		

Temperatures

Operating temperature range	-40...55 °C
-----------------------------	-------------

General data

Colour	grey	EMC version	No
Filter class	G 4	Height of installation cut-outs	125 mm
Material	Thermoplastic	Mounting depth	26 mm
Mounting height	5 mm	Operating temperature range	-40...55 °C
Protection class (UL)	Type 12	Type of mounting	Snap-on
UL 94 flammability rating	V-0	Width of installation cut-outs	125 mm
With filter	Yes		

Classifications

ETIM 6.0	EC0025 13	ETIM 7.0	EC0025 13
ETIM 8.0	EC0025 13	ETIM 9.0	EC0025 13
ECLASS 9.1	27-18-07-06	ECLASS 10.0	27-18-07-06
ECLASS 11.0	27-18-07-06	ECLASS 12.0	27-18-07-06
ECLASS 13.0	27-18-07-06		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E252704

Downloads

User Documentation	Installation- and operating instructions
Catalogues	Catalogues in PDF-format

EF 20 55 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Filter fan**

The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

General ordering data

Type	FF-FIMT 2X 55	Version
Order No.	2556670000	Filter mat, IP55, white
GTIN (EAN)	4050118567298	
Qty.	5 pc(s).	