

FH-TCO 200W 230V BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

General ordering data

| | |
|-----------------|--------------------------------|
| Version | Heating panel fan, IP20, black |
| Order No. | 2558010000 |
| Type | FH-TCO 200W 230V BK |
| GTIN (EAN) | 4050118568653 |
| Qty. | 1 pc(s). |
| Available until | 2023-11-10 |

FH-TCO 200W 230V BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 126 mm | Depth (inches) | 4.961 inch |
| Height | 142 mm | Height (inches) | 5.591 inch |
| Width | 88 mm | Width (inches) | 3.465 inch |
| Net weight | 740 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...70 °C |
|-----------------------------|-------------|

General data

| | | | |
|--------------------------------|----------------------|----------------------|----------------|
| Continuous heat output at 10°C | 200 W | Inrush current | max. 9 A |
| Operating temperature range | -40...70 °C | Operating voltage | 230 V |
| Protection degree | IP20 | Type of connection | Spring contact |
| Type of mounting | Rail, Screw mounting | With room thermostat | No |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000737 | ETIM 7.0 | EC000737 |
| ETIM 8.0 | EC000737 | ETIM 9.0 | EC000737 |
| ECLASS 9.1 | 27-18-07-10 | ECLASS 10.0 | 27-18-07-10 |
| ECLASS 11.0 | 27-18-07-10 | ECLASS 12.0 | 27-18-07-10 |
| ECLASS 13.0 | 27-18-07-10 | | |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E497839 |

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | EU Declaration of Conformity EU Declaration of Conformity |
| Engineering Data | CAD data – STEP |
| User Documentation | Operating instructions |
| Catalogues | Catalogues in PDF-format |

FH-TCO 200W 230V BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Hygrostat**

Filter fans and cabinet heaters are ideally complemented by thermostats and hygrostats. Filter fans and heaters only work when cooling or heating is actually necessary. Because of the demand-oriented thermostats and hygrostats increase the energy efficiency and save costs.

Hygrostat: Humidity control and condensation protection, especially in high humidity environments.

General ordering data

| | | |
|------------|----------------------------|-----------------------------------|
| Type | HYSW 40-90% R.F. CO | Version |
| Order No. | 2558270000 | Humidity switch, IP20, grey white |
| GTIN (EAN) | 4050118568929 | |
| Qty. | 1 pc(s). | |