

HDC 24B ABU EMC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The new Weidmüller RockStar® IP65 EMV enclosures are ideally suited for use in the harshest environmental conditions and provide protection against electromagnetic interference. A heavy-duty connector consists of a connector insert and its protective housing. The new plastic straps are easy to lock and can be replaced at any time. All Weidmüller RockStar® enclosures are made of high quality die-cast aluminium. This makes them impact- and corrosion-resistant, yet compact and lightweight.

General ordering data

Version	HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side, Side-locking clamp replaceable
Order No.	2527810000
Type	HDC 24B ABU EMC
GTIN (EAN)	4050118618297
Qty.	1 pc(s).

HDC 24B ABU EMC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	141 mm	Depth (inches)	5.551 inch
Height	30 mm	Height (inches)	1.181 inch
Width	47 mm	Width (inches)	1.85 inch
Net weight	152 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

General data

EMC housings	Yes	Housing main material	diecast aluminium
Material of locking element	PA 66/6, Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish	Powder coating	UL 94 flammability rating	V-0

Version

BG	8	Clamp version	Side-locking clamp
Colour (RAL)	RAL 9011	Cover	without cover
Design of housing		Design of locking system	Side-locking clamp on lower side, Side-locking clamp replaceable
	Bulkhead housing		
Sealing	FPM	Size	8
Suitable for ModuPlug®	Yes	Top part/bottom part/lid	lower part
Type	Bulkhead (feed-through)		

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ECLASS 9.0	27-44-02-02	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-02	ECLASS 11.0	27-44-02-02
ECLASS 12.0	27-44-02-02	ECLASS 13.0	27-44-02-02

Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Petrol
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Resistant
Substance	Ozone
Chemical resistance	Resistant

HDC 24B ABU EMC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Downloads

Engineering Data	CAD data – STEP
Product Change Notification	20220214 Technical change to HDC housings 20220214 Technische Änderung bei HDC-Gehäusen
Catalogues	Catalogues in PDF-format

HDC 24B ABU EMC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

