

**TCC 6.4/51 BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****Adjustable cross-connections**

Increase the flexibility of your cross-connections. The TERMSERIES CROSS-CONNECTION (TCC) enables individually adjustable cross-connections with up to 51 poles. The maximum number of pluggable poles has been increased to 32 poles. The strip material can be shortened to the required length very easily. The cross-connectors convince thanks to their easy handling and visibility as well as their universal connection possibilities. An additional web prevents the spring from deforming during assembly.

- Individually adjustable cross-connection with 51 poles
- Additional bar to avoid deformation of the spring
- Increased cross-connection – up to 32 poles possible
- Vibration resistance

**General ordering data**

|            |                             |
|------------|-----------------------------|
| Version    | TERMSERIES, Cross-connector |
| Order No.  | <a href="#">2556450000</a>  |
| Type       | TCC 6.4/51 BL               |
| GTIN (EAN) | 4050118566963               |
| Qty.       | 10 pc(s).                   |

## TCC 6.4/51 BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 4.8 mm   | Depth (inches)  | 0.189 inch  |
| Height     | 13.1 mm  | Height (inches) | 0.516 inch  |
| Width      | 323.4 mm | Width (inches)  | 12.732 inch |
| Net weight | 12 g     |                 |             |

## Temperatures

|                     |                |                       |                |
|---------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -40 °C...60 °C |
|---------------------|----------------|-----------------------|----------------|

## Rated data UL

|                    |      |
|--------------------|------|
| Rated current (UL) | 10 A |
|--------------------|------|

## General data

|                                    |                          |         |  |
|------------------------------------|--------------------------|---------|--|
| Version                            | can be cut to length     |         |  |
| Colour                             | blue                     |         |  |
| UL94 flammability rating component | Component                | Housing |  |
|                                    | UL94 flammability rating | V-0     |  |

## Insulation coordination

|               |       |
|---------------|-------|
| Rated voltage | 300 V |
|---------------|-------|

## Connection data

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 6.4 mm |
|-----------------|--------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002586    | ETIM 7.0    | EC002586    |
| ETIM 8.0    | EC002586    | ETIM 9.0    | EC002586    |
| ECLASS 9.1  | 27-37-16-92 | ECLASS 10.0 | 27-37-16-92 |
| ECLASS 11.0 | 27-37-16-92 | ECLASS 12.0 | 27-37-16-92 |
| ECLASS 13.0 | 27-37-16-92 |             |             |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>   |
| User Documentation | <a href="#">Beipackzettel / Package Insert – multilingual</a><br><a href="#">Beipackzettel / Package Insert</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>  |


## TCC 6.4/51 BL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Product image



## Dimensional drawing



## TCC 6.4/51 BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Cutting and notching tools for cross-connections



- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

## General ordering data

|            |                            |                                     |
|------------|----------------------------|-------------------------------------|
| Type       | KT ZQV                     | Version                             |
| Order No.  | <a href="#">9002170000</a> | Cutting tool for one-hand operation |
| GTIN (EAN) | 4032248291670              |                                     |
| Qty.       | 1 pc(s).                   |                                     |
| Type       | WAW 1 NEUTRAL              | Version                             |
| Order No.  | <a href="#">9004500000</a> | Miscellaneous tools                 |
| GTIN (EAN) | 4008190053925              |                                     |
| Qty.       | 1 pc(s).                   |                                     |

## Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | KT 14                      | Version  |
| Order No.  | <a href="#">1157820000</a> | Cutting tools, Cutting tool for one-hand operation |
| GTIN (EAN) | 4032248945344              |  |
| Qty.       | 1 pc(s).                   |  |

## TCC 6.4/51 BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com

## Drawings

## Miscellaneous

## Type code TERMSERIES accessories



Type codes