

**CUTFIX 8 INTERFACE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

**General ordering data**

Version	Cutting machine
Order No.	<a href="#">2580010000</a>
Type	CUTFIX 8 INTERFACE
GTIN (EAN)	4050118605839
Qty.	1 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2025-01-06
Replacement parts	<a href="#">9054740000</a>
Alternative product	<a href="#">2797190000</a>

Creation date May 1, 2024 8:24:12 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

**CUTFIX 8 INTERFACE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	360 mm	Depth (inches)	14.173 inch
Height	470 mm	Height (inches)	18.504 inch
Width	380 mm	Width (inches)	14.961 inch
Net weight	20,809 g		

**Automatic cutting**

Amount pre-selection, max.	Adjustable part quantity code	Aperture (max. diameter)	8 mm outer diameter
Correction for length	Slip correction in mm can be programmed to suit the part.	Display	LCD display
Drive	electrical	Electrical connection	100 - 240 V / 50 Hz / 240 VA
Feeding speed, max.	1.5 m/s	Flexible/solid individual conductors	max. 10 mm <sup>2</sup> / max. 2.5 mm <sup>2</sup>
Interface	USB 1.1, USB 2.0	Keyboard	Touch display
Length pre-selection, max.	999,999 mm	Length pre-selection, min.	2 mm
Software	for data exchanging with IBM-compatible PC, Integrated interface to read CAE data	Storage	Up to 2,000 cutting jobs

**Classifications**

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-03
ECLASS 10.0	17-13-01-03	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CUTFIX 8 INTERFACE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Replacement parts****Accessories / replacement parts**

- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

**General ordering data**

Type	AIMESA V CUTFIX	Version
Order No.	<a href="#">9054740000</a>	Accessories, Replacement part
GTIN (EAN)	4032248104512	
Qty.	1 pc(s).	