

P BAG XL SET 13**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Version	Tools, Accessories
Order No.	2602230000
Type	P BAG XL SET 13
GTIN (EAN)	4050118657814
Qty.	1 pc(s).

P BAG XL SET 13**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	220 mm	Depth (inches)	8.661 inch
Height	60 mm	Height (inches)	2.362 inch
Width	320 mm	Width (inches)	12.598 inch
Net weight	1,809 g		

Technical data

Description of article	Toolbag, fitted
------------------------	-----------------

Classifications

ETIM 6.0	EC000181	ETIM 7.0	EC000181
ETIM 8.0	EC000181	ETIM 9.0	EC000181
ECLASS 9.0	21-10-01-90	ECLASS 9.1	21-10-01-90
ECLASS 10.0	21-10-01-90	ECLASS 11.0	21-10-01-90
ECLASS 12.0	21-10-01-90	ECLASS 13.0	21-10-01-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Downloads

Catalogues	Catalogues in PDF-format
------------	--

P BAG XL SET 13**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****with LED Display**

The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

General ordering data

Type	VT COMBI PRO	Version
Order No.	9918860000	Testing tools, 2-pole voltage tester
GTIN (EAN)	4032248405749	
Qty.	1 pc(s).	

VDE-insulated combination pliers

When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Type	KBZ 180	Version
Order No.	9046290000	Pliers
GTIN (EAN)	4032248356485	
Qty.	1 pc(s).	

P BAG XL SET 13

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIS SLIM 0.6X3.5X100	Version
Order No.	2749610000	Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade
GTIN (EAN)	4050118896350	thickness (A): 0.6 mm
Qty.	1 pc(s).	
Type	SDIS SLIM 0.8X4.0X100	Version
Order No.	2749620000	Mounting tool, Blade width (B): 4 mm, Blade length: 100 mm, Blade
GTIN (EAN)	4050118896367	thickness (A): 0.8 mm
Qty.	1 pc(s).	

unfitted



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Type	P BAG BIG	Version
Order No.	2576620000	Tools, Accessories
GTIN (EAN)	4050118650594	
Qty.	1 pc(s).	

P BAG XL SET 13**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Tools**

- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

Type	STRIPPER ROUND TOP	Version
Order No.	9918050000	Sheathing strippers
GTIN (EAN)	4032248359165	
Qty.	1 pc(s).	

Tools

- Simple, fast and accurate stripping of insulation of all conventional round cables from 4 to 37 mm²
- Knurled screw at end of handle for setting the cutting depth (setting the cutting depth prevents damage to inner conductor)

General ordering data

Type	SLICER NO 16	Version
Order No.	9918070000	Sheathing strippers
GTIN (EAN)	4032248359189	
Qty.	1 pc(s).	

P BAG XL SET 13

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version
Order No.	9005000000	Tools, Stripping and cutting tool
GTIN (EAN)	4008190072506	
Qty.	1 pc(s).	

Crosshead screwdriver, Phillips



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIK SLIM PH2 X 100	Version
Order No.	2749660000	Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A): 2
GTIN (EAN)	4050118896404	
Qty.	1 pc(s).	
Type	SDIK SLIM PH1 X 80	Version
Order No.	2749650000	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
GTIN (EAN)	4050118896398	
Qty.	1 pc(s).	

P BAG XL SET 13**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Cutting tools**

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Type	KT 8	Version
Order No.	9002650000	Cutting tools, Cutting tool for one-hand operation
GTIN (EAN)	4008190020163	
Qty.	1 pc(s).	