


HS-FR 9.5-19.1/50 MM Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 9.5 - 19.1 mm, 49.8 x 30.4 mm, yellow
Order No.	2621870000
Type	HS-FR 9.5-19.1/50 MM Y
GTIN (EAN)	4050118625172
Qty.	400 pc(s).
compatible printer	2599430000 2599440000

HS-FR 9.5-19.1/50 MM Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.77 mm	Depth (inches)	0.03 inch
Height	49.8 mm	Height (inches)	1.961 inch
Width	30.4 mm	Width (inches)	1.197 inch
Net weight	1.6 g		

Temperatures

Operating temperature range	-55...125 °C
-----------------------------	--------------

General data

Colour	yellow	Halogen	No
Material	Polyolefine	Operating temperature range	-55...125 °C
Operating temperature range, max.	125 °C	Operating temperature range, min.	-55 °C
Size of labelling field	30.4 x 49.8 mm	Width	30.4 mm

Conductor and cable markers

Conductor O.D.	9.5 - 19.1 mm	Conductor O.D., max.	19.1 mm
Conductor O.D., min.	9.5 mm	Conductor cross-section, max.	70 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 70 mm ²
Halogen	No	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Wire connection cross section AWG, max.	AWG 2/0
Wire connection cross section AWG, min.	AWG 6		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

HS-FR 9.5-19.1/50 MM Y

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

