

CABTITE BP 35MM PA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Similar to illustration

The blanking plugs are used for the safe closing of un-needed cable passages in the sealing elements.

General ordering data

| | |
|------------|--|
| Version | Blind plug, Cabtite (cable entry system), Polyamide, red, Height: 35 mm, Width: 35 mm, Depth: 35 mm, -60 °C...100 °C, IP66 |
| Order No. | 2652480000 |
| Type | CABTITE BP 35MM PA |
| GTIN (EAN) | 4050118662580 |
| Qty. | 10 pc(s). |

CABTITE BP 35MM PA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|----------|-------|-----------------|------------|
| Depth | 35 mm | Depth (inches) | 1.378 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Width | 35 mm | Width (inches) | 1.378 inch |
| Length | 35 mm | Length (inches) | 1.378 inch |
| Diameter | 35 mm | Net weight | 12.3 g |

Temperatures

| | |
|-----------------------|------------------|
| Operating temperature | -60 °C... 100 °C |
|-----------------------|------------------|

General information

| | | | |
|----------------------------|-------|----------------------------|-----------|
| Halogen | No | Material | Polyamide |
| Outer cable diameter, max. | 35 mm | Outer cable diameter, min. | 35 mm |
| Protection degree | IP66 | UL 94 flammability rating | V-0 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000879 | ETIM 7.0 | EC000879 |
| ETIM 8.0 | EC000879 | ETIM 9.0 | EC000879 |
| ECLASS 9.0 | 27-14-44-21 | ECLASS 9.1 | 27-14-44-21 |
| ECLASS 10.0 | 27-14-44-21 | ECLASS 11.0 | 27-14-44-21 |
| ECLASS 12.0 | 27-14-08-07 | ECLASS 13.0 | 27-14-08-07 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| User Documentation | Cabtite Installation Instructions |
| Catalogues | Catalogues in PDF-format |