

**SAIEND 1/4 M8G 3P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Passive M12 distributors are available in all conceivable forms and configurations. Furthermore, a number of special versions, e.g. SAI distributors for EX zones or the ergonomic M8, are available only from Weidmüller. These innovative products are backed up by numerous proprietary rights.

**General ordering data**

Version	M8, LED: , LED initiator: , Wiring type:
Order No.	<a href="#">2662450000</a>
Type	SAIEND 1/4 M8G 3P
GTIN (EAN)	4050118677379
Qty.	1 pc(s).

**SAIEND 1/4 M8G 3P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	5 g
------------	-----

**Temperatures**

Operating temperature	-25 - 85
-----------------------	----------

**General technical data**

Protection degree	IP67	Number of poles	4
Connection thread	M8	Pollution severity	3
Plugging cycles	≥ 100		

**Technical data cable**

Number of poles	4
-----------------	---

**Classifications**

ETIM 6.0	EC000448	ETIM 7.0	EC000448
ETIM 8.0	EC000448	ETIM 9.0	EC000448
ECLASS 9.0	19-07-04-03	ECLASS 9.1	19-17-01-90
ECLASS 10.0	19-07-04-03	ECLASS 11.0	19-07-04-03
ECLASS 12.0	19-07-04-03	ECLASS 13.0	19-07-04-03

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd55fbf5cb55

**Approvals**

Approvals

**Downloads**



Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## SAIEND 1/4 M8G 3P

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings



**SAIEND 1/4 M8G 3P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	DEK 5/5 MC NE WS	Version
Order No.	<a href="#">1609801044</a>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397111	Weidmueller, white
Qty.	1,000 pc(s).	