

## HDC DSUB 15 FC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Order No.	<a href="#">2664460000</a>
Type	HDC DSUB 15 FC
GTIN (EAN)	4050118786514
Qty.	100 pc(s).

## HDC DSUB 15 FC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	6 g
------------	-----

## Design

Product family	RockStar® HDC SUBD	Product type	Insert
Type	Female	Type of connection	Crimp connection

## Electrical data

Volume resistance	≤10 mΩ	Insulation strength	≥10 GΩ
Rated current	7 A	Rated voltage	125 V
Test voltage $V_{\text{eff}}$ Contact/contact	1 kV	Test voltage $V_{\text{eff}}$ Contact/earth	1.2 kV

## General descriptions

Outgoing elbow	180°	Number of poles	15
Plugging cycles	500		

## Material

Insulating material	Thermoplastic	Colour	black (similar to RAL 9005)
Colour (RAL)	RAL 9005	UL 94 flammability rating	V-0
Contact base material	Copper alloy	Contact surface	Gold-plated
Shielding material	Sheet steel	Shield surface	tinned

## Classifications

ETIM 6.0	EC001132	ETIM 7.0	EC001132
ETIM 8.0	EC001132	ETIM 9.0	EC001132
ECLASS 9.0	27-44-03-02	ECLASS 9.1	27-44-03-90
ECLASS 10.0	27-44-03-02	ECLASS 11.0	27-44-03-02
ECLASS 12.0	27-44-03-02	ECLASS 13.0	27-44-03-02

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**HDC DSUB 15 FC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Crimp contacts**

Weidmüller's SUB-D connector range includes Sub-D inserts and contacts for applications with a wide range of requirements, metal hoods, which are particularly suitable for robust applications. Accessories tailored to the application complete the product range. The SUB-D connector has been the proven interface for bus signals in industrial applications for many years. SUB-D connectors are manufactured in countless numbers of poles, variants, housings, contacts and designs. The long market presence and continuous development have made the D-Sub an all-round interface for demanding industrial applications.

**General ordering data**

Type	HDC DSUB CF 22-18
Order No.	<a href="#">2664510000</a>
GTIN (EAN)	4050118786552
Qty.	100 pc(s).

Type	HDC DSUB CF 26 - 22
Order No.	<a href="#">2664610000</a>
GTIN (EAN)	4050118786576
Qty.	100 pc(s).

**Size SUBD 2-15**

Weidmüller's SUB-D connector range includes Sub-D inserts and contacts for applications with a wide range of requirements, metal hoods, which are particularly suitable for robust applications. Accessories tailored to the application complete the product range. The SUB-D connector has been the proven interface for bus signals in industrial applications for many years. SUB-D connectors are manufactured in countless numbers of poles, variants, housings, contacts and designs. The long market presence and continuous development have made the D-Sub an all-round interface for demanding industrial applications.

**General ordering data**

Type	HDC DSUB 15 TOS M3
Order No.	<a href="#">2664680000</a>
GTIN (EAN)	4050118786644
Qty.	10 pc(s).

Type	HDC DSUB 15 TO UNC
Order No.	<a href="#">2664690000</a>
GTIN (EAN)	4050118786651
Qty.	10 pc(s).