

CMA-81-2000-5A-10VA-0,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Plug-on current transformers**

Plug-on current transformers are especially suitable for mounting on the busbar.

The advantages of this type are: screwless connection technology with tension clamp connection, time-saving connection option for solid and flexible conductors, shock-resistant and vibration-proof, high mechanical holding forces and high current resistance.

General ordering data

Version	Primary current: 2000 A, Secondary current max.: 5 A, Load: , Tolerance class: , closed current transformer
Order No.	2680240000
Type	CMA-81-2000-5A-10VA-0,5
GTIN (EAN)	4050118696592
Qty.	1 pc(s).
Manufacturer	MBS AG

CMA-81-2000-5A-10VA-0,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	134 mm	Length (inches)	5.276 inch
Net weight	570 g		

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	54 mm
Rail	60 x 30 mm, 80 x 10 mm	Installation location	Indoor use

Electrical attributes

Primary current	2,000 A	Secondary current	0...5 A
-----------------	---------	-------------------	---------

Technical properties

Nominal frequency	50 Hz	Protection degree	IP20
Thermal rated continuous current $I_{\text{thermal}} 1.2 \times I_{\text{rated}}$			

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ECLASS 9.0	27-21-09-02	ECLASS 9.1	27-21-09-02
ECLASS 10.0	27-21-09-02	ECLASS 11.0	27-21-09-02
ECLASS 12.0	27-21-09-02	ECLASS 13.0	27-21-09-02

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	UL- certificate UKCA Declaration of Conformity Declaration of Conformity
Engineering Data	CAD data – STEP
Technical Documentation	3D drawing
User Documentation	Device description – instruction sheet english.pdf Device description – Betriebsanleitung deutsch
Catalogues	Catalogues in PDF-format

CMA-81-2000-5A-10VA-0,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

