PRINTJET CONNECT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The PrintJet CONNECT is the consistent further development of our tried-and-tested PrintJet series. Focusing on the modern needs of industry and panel building, it combines maximum process and cost efficiency with intelligent networking and complete data consistency. For example, you can use existing data directly in the marking process – for working more efficiently and with a minimal error rate.

General ordering data

Version	Marking systems, Ink jet technology, 1200 DPI, Multicard, MetalliCard
Order No.	2715590000
Type	PRINTJET CONNECT
GTIN (EAN)	4064675016922
Qty.	1 pc(s).

PRINTJET CONNECT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	930 mm	Depth (inches)	36.614 inch
Height	454 mm	Height (inches)	17.874 inch
Width	590 mm	Width (inches)	23.228 inch
Net weight	46,000 g		

Labelling systems

Fueling system	Ink cartridge, CMYK	Included in delivery	PrintJet CONNECT, Power cable, USB cable, W-LAN stick, 1 unit DEK 5/5, 2 x PrintJet Cleaner tissues, DVD with M-Print® PRO, Quick start guide, user manual D/EN, all other 23 languages on DVD as a PDF, Dust cover
Interface	USB, LAN, Wi-Fi	Marker type	Multicard, MetalliCard
Operating system	Windows 7, Windows 8, Windows 8.1, Windows 10, Windows 11	Print resolution, max.	1,200 DPI
Printer driver	Windows 7, Windows 8, Windows 8.1, Windows 10	Printing method	Ink jet technology
Printing speed	Depends on printing quality	Software	M-Print® PRO
Voltage supply	230 V AC / 16 A, 115 V AC / 20 A		

Classifications

ETIM 6.0	EC000610	ETIM 7.0	EC000610
ETIM 8.0	EC000610	ETIM 9.0	EC000610
ECLASS 9.0	24-32-11-90	ECLASS 9.1	24-32-11-02
ECLASS 10.0	24-32-11-90	ECLASS 11.0	24-32-11-90
ECLASS 12.0	24-32-11-90	ECLASS 13.0	24-32-11-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Hexahydromethylphthalic anhydride 19438-60-9 Cyclohexane-1,2-dicarboxylic anhydride 85-42-7 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol 79-94-7
SCIP	1019ebc1-7078-40d9-974d-3aa332713b10

Approvals

Approvals	
ROHS	Conform

PRINTJET CONNECT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	MET Certification Record PrintJet CONNECT Declaration of Conformity UKCA Declaration of Conformity acma RCM Declaration of Conformity Korea Certification PrintJet CONNECT
Software	Firmware – PrintJet CONNECT Firmware 1.2.5 via PC Firmware – PrintJet CONNECT Firmware 1.2.5 via USB-Stick
User Documentation	Manual PrintJet CONNECT - BG Manual PrintJet CONNECT - CN Manual PrintJet CONNECT - CZ Manual PrintJet CONNECT - DE Manual PrintJet CONNECT - DK Manual PrintJet CONNECT - EL Manual PrintJet CONNECT - EN Manual PrintJet CONNECT - ES Manual PrintJet CONNECT - ET Manual PrintJet CONNECT - FI Manual PrintJet CONNECT - FR Manual PrintJet CONNECT - HU Manual PrintJet CONNECT - IT Manual PrintJet CONNECT - LT Manual PrintJet CONNECT - LV Manual PrintJet CONNECT - NL Manual PrintJet CONNECT - PL Manual PrintJet CONNECT - RO Manual PrintJet CONNECT - RU Manual PrintJet CONNECT - SK Manual PrintJet CONNECT - SL Manual PrintJet CONNECT - SV Manual PrintJet CONNECT - PT Manual PrintJet CONNECT - KO Manual PrintJet CONNECT - PT BR Instruction FW Update PrintJet CONNECT
Catalogues	Catalogues in PDF-format

PRINTJET CONNECT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

PrintJet CONNECT



Accessories and consumables for the PrintJet CONNECT

General ordering data

Type	PJ CON INK C
Order No.	2715610000
GTIN (EAN)	4064675041573
Qty.	1 pc(s).
Type	PJ CON INK Y
Order No.	2715630000
GTIN (EAN)	4064675041580
Qty.	1 pc(s).
Type	PJ CON WASTE PAD
Order No.	2715660000
GTIN (EAN)	4064675042051
Qty.	1 pc(s).
Type	PJ CON FLUID SET
Order No.	2715650000
GTIN (EAN)	4064675036036
Qty.	1 pc(s).
Type	PJ CON INK K
Order No.	2715640000
GTIN (EAN)	4064675041887
Qty.	1 pc(s).
Type	PJ CON INK SET
Order No.	2715600000
GTIN (EAN)	4064675041566
Qty.	1 pc(s).
Type	PJ CON TEXTILE COVER
Order No.	2715670000
GTIN (EAN)	4064675042068
Qty.	1 pc(s).
Type	PJ CON INK M
Order No.	2715620000
GTIN (EAN)	4064675042044
Qty.	1 pc(s).
Type	PJ CON WIFI STICK
Order No.	2715680000
GTIN (EAN)	6955690002749
Qty.	1 pc(s).
Type	PJ CON SERVICE FLAP
Order No.	2715690000
GTIN (EAN)	4064675042082
Qty.	1 pc(s).

PRINTJET CONNECT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	PJ CON CLEANING UNIT
Order No.	2715700000
GTIN (EAN)	4064675042099
Qty.	1 pc(s).

M-Print® PRO



The M-Print® PRO printing and ordering software for markers and labels® is a professional Windows®-based solution for both printing and ordering Weidmüller labels and markers . This software allows you to optimise the process of identifying electrical equipment. You can design and order your marking materials easily, professionally and quickly: with text, frames, lines, graphics, bar codes, serial numbers and photos.

- Integrated product catalogue for all labels and markers, incl. images, link to the website and product data sheet
- Markers and labels can be designed on as many levels as required
- Customised formatting of individual text characters (RTF)
- Copy and paste texts and their formats
- Available in 20 languages supporting UNICODE
- Data entry in labels and spreadsheets, or directly in Microsoft Excel
- Creation of scales; numeric and alpha-numeric counters and sequences
- Extensive range of image formats (*.bmp, *.wmf, *.png, *.ico, *.jpeg, *.jpg, *.tif, *.gif)
- Image library including symbols used in electrical engineering
- Product-printer allocation options, e.g. ESG 9/20 to PrintJet; MultiMark on thermotransfer printer
- Online update service via the Internet
- Weidmueller Configurator (WMC) interface
- Import wizard for a number of file formats (*.txt, *.csv, *.xml, etc.) for creating your own import scripts
- Transfer of data from CAE systems
- Permanent print preview: see what the printout will look like even at the design phase, WYSIWYG editing
- Supported output devices: All Weidmueller printers (e.g. PrintJet CONNECT, THM MultiMark, etc.) and standard printers with Microsoft Windows® driver
- Optimal and fast adaptation of output devices
- Multi-level structuring of markers and labels

General ordering data

Type	M-PRINT PRO	Version
Order No.	1905490000	Software for markings, Software, Windows 7, Windows 8, Windows
GTIN (EAN)	4032248526291	8.1, Windows 10, Windows 11, Printer software
Qty.	1 pc(s).	