


CC-DT 85/54 K MC NE BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

We support our customers in the food industry with detectable marking solutions to ensure the high standards required within the framework of the HACCP concept. Thanks to a metallic filler, our detectable MultiCards can be reliably identified by metal and X-ray detectors. This minimises the risk of product contamination in the production process. Maximum safety is ensured with important product properties, such as corrosion resistance or higher ageing resistance to UV radiation in indoor areas and heat. These properties are regularly tested and confirmed in our own accredited laboratory. Not suitable for direct food contact.

- Detectable by metal and X-ray detectors
- Visually recognisable by blue colour
- Corrosion resistant metallic filler
- Clear and resistant print image
- Available in different versions for a wide variety of marking requirements

General ordering data

| | |
|--------------------|--|
| Version | ClipCard, Device markers, 54 x 85 mm, blue |
| Order No. | 2737750000 |
| Type | CC-DT 85/54 K MC NE BL |
| GTIN (EAN) | 4064675028147 |
| Qty. | 10 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

CC-DT 85/54 K MC NE BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.8 mm | Depth (inches) | 0.031 inch |
| Height | 54 mm | Height (inches) | 2.126 inch |
| Width | 85 mm | Width (inches) | 3.346 inch |
| Net weight | 12.29 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

General data

| | | |
|---|------------------------------|-----------|
| Adhesive | Double-sided adhesive tape | |
| Colour | blue | |
| Detectible in accordance with Rondotest | 4.7 mm Al | |
| Halogen | No | |
| Material | Polyamide 66 | |
| Number of markers per combination | 1 MultiCard = Device markers | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Operating temperature range | -40...60 °C | |
| Operating temperature range, max. | 60 °C | |
| Operating temperature range, min. | -40 °C | |
| Printed characters | neutral | |
| Recommended industries | Food processing industry | |
| UL 94 flammability rating | HB | |
| Width | 85 mm | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads


| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

CC-DT 85/54 K MC NE BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



CC-DT 85/54 K MC NE BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories****General ordering data**

| | | |
|------------|----------------------------|---|
| Type | CC-DT-H 85/54 BL | Version |
| Order No. | 2737770000 | ClipCard, Accessories, 90 x 58 mm, blue |
| GTIN (EAN) | 4064675211167 | |
| Qty. | 20 pc(s). | |