

**SCT 7.9/520****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

**General ordering data**

Version	Cable ties, 7.9 x 520 mm, Stainless steel 1.4404 (316L), 1112 N
Order No.	<a href="#">2791470000</a>
Type	SCT 7.9/520
GTIN (EAN)	4064675070993
Qty.	100 pc(s).

## SCT 7.9/520

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

Depth	0.26 mm	Depth (inches)	0.01 inch
Height	520 mm	Height (inches)	20.472 inch
Width	7.9 mm	Width (inches)	0.311 inch
Net weight	9.3 g		

## Temperatures

Operating temperature range	-40...300 °C	Installation temperature	-40
-----------------------------	--------------	--------------------------	-----

## Installation materials

Bundle diameter, max.	150 mm	Bundle diameter, min.	20 mm
Cable diameter, max.	150 mm	For re-opening	No
Halogen	No	Material	Stainless steel 1.4404 (316L)
Operating temperature range, max.	300 °C	Operating temperature range, min.	-40 °C
Tensile strength	1,112 N	Tensile strength (Pound-force)	250 lbf

## Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E524836

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## SCT 7.9/520

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

