

CA 100 DUO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	2740900000
Type	CA 100 DUO
GTIN (EAN)	4050118835700
Qty.	1 pc(s).
Replacement parts	2007380000 2912430000

CA 100 DUO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	550 mm	Depth (inches)	21.653 inch
Height	440 mm	Height (inches)	17.323 inch
Width	415 mm	Width (inches)	16.339 inch
Net weight	40,000 g		

PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 - 5.5 bar	Consumables	with plastic collar
Crimping	Trapezoidal	Crimping length	8 - 18 mm
Drive	Electropneumatic	Electrical connection	100-240 V / 50/60 Hz / 100 VA
Pulse time	approx. 3 s	Stripping range	6 - 10 mm ² (4 mm ² opt.) / AWG 10-8 (AWG 12 opt.)

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Flyer - CA 100 DUO Manual CA 100 DUO EN DE
Catalogues	Catalogues in PDF-format

CA 100 DUO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Replacement parts****Accessories / replacement parts**

- for automatic stripping of individual wires
- stripping of flexible wires according to DIN VDE 0295, Cl. 5
- Partial stripping of insulation, the isolation remains on wire end
- Change of tools not necessary
- Quick and easy setting for the proper cross-section
- Electric drive

General ordering data

Type	AIMESA VRM 3,49	Version
Order No.	2007380000	Accessories, Set of cutters
GTIN (EAN)	4050118392753	
Qty.	1 pc(s).	

Accessories / replacement parts

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Type	CA 100 DUO S	Version
Order No.	2912430000	Automatic machines, Automatic stripper and crimper
GTIN (EAN)	4099986536005	
Qty.	1 pc(s).	

CA 100 DUO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

packed loose in polythene bag



- supplied loose in polybag
- DIN colour code
- other colour code

General ordering data

Type	H4,0/26D GR	Version	Packaging
Order No.	9019210000	Wire-end ferrule, Standard, 20 mm, 18 mm, grey	loose
GTIN (EAN)	4008190002336		
Qty.	100 pc(s).		
Type	H4,0/18T OR	Version	Packaging
Order No.	9021100000	Wire-end ferrule, Standard, 12 mm, 10 mm, orange	loose
GTIN (EAN)	4008190061708		
Qty.	500 pc(s).		
Type	H4,0/20D GR	Version	Packaging
Order No.	9019200000	Wire-end ferrule, Standard, 14 mm, 12 mm, grey	loose
GTIN (EAN)	4008190126575		
Qty.	500 pc(s).		
Type	H4,0/18D GR	Version	Packaging
Order No.	9019190000	Wire-end ferrule, Standard, 12 mm, 10 mm, grey	loose
GTIN (EAN)	4008190141349		
Qty.	500 pc(s).		
Type	H4,0/26T OR	Version	Packaging
Order No.	9021120000	Wire-end ferrule, Standard, 20 mm, 18 mm, orange	loose
GTIN (EAN)	4008190092825		
Qty.	100 pc(s).		
Type	H4,0/20T OR	Version	Packaging
Order No.	9021110000	Wire-end ferrule, Standard, 14 mm, 12 mm, orange	loose
GTIN (EAN)	4008190035754		
Qty.	500 pc(s).		

CA 100 DUO

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Conductor nom. cross-section 10mm²

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H10,0/22 EB	Version	Packaging
Order No.	0534200000	Wire-end ferrule, Standard, 15 mm, 12 mm, Ivory	loose
GTIN (EAN)	4008190033460		
Qty.	100 pc(s).		
Type	H10,0/28D R	Version	Packaging
Order No.	9019250000	Wire-end ferrule, Standard, 21 mm, 18 mm, red	loose
GTIN (EAN)	4008190041410		
Qty.	100 pc(s).		
Type	H10,0/22T BR	Version	Packaging
Order No.	9021150000	Wire-end ferrule, Standard, 15 mm, 12 mm, brown	loose
GTIN (EAN)	4008190086886		
Qty.	100 pc(s).		
Type	H10,0/28T BR	Version	Packaging
Order No.	9021160000	Wire-end ferrule, Standard, 21 mm, 18 mm, brown	loose
GTIN (EAN)	4008190041915		
Qty.	100 pc(s).		
Type	H10,0/22D R	Version	Packaging
Order No.	9019240000	Wire-end ferrule, Standard, 15 mm, 12 mm, red	loose
GTIN (EAN)	4008190075385		
Qty.	100 pc(s).		
Type	H10,0/28 EB	Version	Packaging
Order No.	0565800000	Wire-end ferrule, Standard, 21 mm, 18 mm, Ivory	loose
GTIN (EAN)	4008190138646		
Qty.	100 pc(s).		

CA 100 DUO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Conductor nom. cross-section 6.0mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H6,0/26 SW	Version	Packaging
Order No.	0565700000	Wire-end ferrule, Standard, 20 mm, 18 mm, black	loose
GTIN (EAN)	4008190026837		
Qty.	100 pc(s).		
Type	H6,0/26T GN	Version	Packaging
Order No.	9021140000	Wire-end ferrule, Standard, 20 mm, 18 mm, green	loose
GTIN (EAN)	4008190022501		
Qty.	100 pc(s).		
Type	H6,0/26D GE	Version	Packaging
Order No.	9019230000	Wire-end ferrule, Standard, 20 mm, 18 mm, yellow	loose
GTIN (EAN)	4008190072117		
Qty.	100 pc(s).		
Type	H6,0/20D GE	Version	Packaging
Order No.	9019220000	Wire-end ferrule, Standard, 14 mm, 12 mm, yellow	loose
GTIN (EAN)	4008190151607		
Qty.	100 pc(s).		
Type	H6,0/20 SW	Version	Packaging
Order No.	0533500000	Wire-end ferrule, Standard, 14 mm, 12 mm, black	loose
GTIN (EAN)	4008190183905		
Qty.	100 pc(s).		
Type	H6,0/20T GN	Version	Packaging
Order No.	9021130000	Wire-end ferrule, Standard, 14 mm, 12 mm, green	loose
GTIN (EAN)	4008190111731		
Qty.	100 pc(s).		