

**ZQV 4N/2 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

Version	Cross-connector (terminal), Plugged, Number of poles: 2, Pitch in mm (P): 6.10, Insulated: Yes, 32 A, black
Order No.	<a href="#">2810840000</a>
Type	ZQV 4N/2 BK
GTIN (EAN)	4064675283454
Qty.	60 pc(s).

## ZQV 4N/2 BK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	27.95 mm	Depth (inches)	1.1 inch
Height	2.8 mm	Height (inches)	0.11 inch
Width	9.9 mm	Width (inches)	0.39 inch
Net weight	1.371 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C...130 °C
---------------------	----------------	-----------------------	-----------------

## Material data

Material	Wemid	Colour	black
UL 94 flammability rating	V-0		

## Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
--------------------------	-----	----------------	---------

## Cross-connector

Rated current, multi-pole	32 A	Type	Cross-connector
---------------------------	------	------	-----------------

## Dimensions

Pitch in mm (P)	6.1 mm
-----------------	--------

## General

Number of poles	2
-----------------	---

## Rating data

Rated current	32 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>