

RC M P2 M20 SP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**DC connector:**

The circular connectors of the DC family are characterised by their compact design. This allows them to be used in a wide range of applications and industries. They are available both as male and female connectors.

General ordering data

Order No.	2860650000
Type	RC M P2 M20 SP
GTIN (EAN)	4064675576662

RC M P2 M20 SP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	12 g
------------	------

Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

Technical data customisable plug-in connectors

Coding	none	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	0.5 mm ²	Connection cross-section, max.	4 mm ²
Connection cross-section, min.	0.5 mm ²	Contact material	Brass
Contact surface	Brass	Housing main material	PA 66
Number of poles	2	Protection degree	IP67, IP68
Rated current	17.5 A	Rated voltage	450 V
Shield connection	No	Type of connection	Screw connection

General data

Housing main material	PA 66	Number of poles	2
Type of connection	Screw connection		

Technical data

Coding	none	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	0.5 mm ²	Contact material	Brass
Contact surface	Brass	Protection degree	IP67, IP68
Rated current	17.5 A	Rated impulse withstand voltage	4 kV
Rated voltage	450 V	Shield connection	No
Stripping length	7 mm	UL 94 flammability rating	V-2

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b64e9137-212c-40f4-8b4a-2cb7feb25f72

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

Creation date May 19, 2024 10:13:53 PM CEST

Catalogue status 04.05.2024 / We reserve the right to make technical changes.

RC M P2 M20 SP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****M20**

Protective caps suitable for FieldPower and WIPL family with round connector

**General ordering data**

Type	PC RC M
Order No.	2820090000
GTIN (EAN)	4064675591405
Qty.	

Round connector M20 mounting tool

Tool:
This tool is ideal for installing the M20 built-in connectors.

**General ordering data**

Type	MTA RC
Order No.	2884950000
GTIN (EAN)	4064675852070
Qty.	

RC M P2 M20 SP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

DC connectors



DC connector:

The circular connectors of the DC family are characterised by their compact design. This allows them to be used in a wide range of applications and industries. They are available both as male and female connectors.

General ordering data

Type	RC F P2 SP
Order No.	2903200000
GTIN (EAN)	4099986122376
Qty.	