

**FSPG BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

**General ordering data**

|            |  |
|------------|--|
| Version    | Fuse holder for feed-through modular terminal, 6.3 A, Pivoting |
| Order No.  | <a href="#">2869680000</a>                                     |
| Type       | FSPG BK  |
| GTIN (EAN) | 4064675623793  |
| Qty.       | 25 pc(s).  |

**FSPG BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 38 mm   | Depth (inches)  | 1.496 inch |
| Height     | 36.5 mm | Height (inches) | 1.437 inch |
| Width      | 6 mm    | Width (inches)  | 0.236 inch |
| Net weight | 5.35 g  |                 |            |

**Temperatures**

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |
|----------------------------------|--------|----------------------------------|--------|

**Material data**

|          |       |                           |       |
|----------|-------|---------------------------|-------|
| Material | Wemid | Insulating material       | Wemid |
| Colour   | black | UL 94 flammability rating | V-0   |

**System specifications**

|                          |    |
|--------------------------|----|
| End cover plate required | No |
|--------------------------|----|

**Additional technical data**

|                  |         |
|------------------|---------|
| Type of mounting | Plugged |
|------------------|---------|

**Rating data**

|                    |   |
|--------------------|---|
| Pollution severity | 3 |
|--------------------|---|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ECLASS 9.0  | 27-14-11-92 | ECLASS 9.1  | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-90 |

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

### FSPG BK

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## FSPG BK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Coding elements



**The pluggable connections for power electronics - optimised for modern drive technologies, e.g. motor starters, frequency converters and servo-controllers.**

OMNIMATE Power sets the new standard – with increased safety and innovative solutions such as the pluggable shield, integrated signal contacts and one-handed operation.

The three product lines offer you further advantages:

- Application-oriented scalability: from the compact 4 mm<sup>2</sup> connector for 29 A (IEC) or 20 A (UL) up to the sturdy 16 mm<sup>2</sup> connector for 76 A (IEC) or 54 A (UL)
- Unlimited usage up to 1,000 V (IEC) or 600 V (UL)
- A variety of application optimised mounting options

Our Service:

Design your individual connectors simply by using the

## General ordering data

| Type       | VDS180 SV7.62              | Version   | Product data | Packaging |
|------------|----------------------------|---|--------------|-----------|
| Order No.  | <a href="#">1853940000</a> | PCB plug-in connector, Accessories, black, Number of poles: 1 |              | Box       |
| GTIN (EAN) | 4032248389513              |   |              |           |
| Qty.       | 50 pc(s).                  |   |              |           |