

FUSE 10X38 1A 1000 VDC GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

The gPV cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards). Made of a ceramic tube with high internal pressure and thermal shock resistance, allowing high switching capacity in a small space. The contacts are made of silver-plated copper and the fusible elements of pure silver to avoid ageing and thus keep the electrical characteristics invariable. They are available in the sizes 10x38 mm, 10x85 mm and 22x58 mm.

General ordering data

Version	Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 1 A
Order No.	2783160000
Type	FUSE 10X38 1A 1000 VDC GPV
GTIN (EAN)	4064675059684
Qty.	10 pc(s).

FUSE 10X38 1A 1000 VDC GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	10 mm	Depth (inches)	0.394 inch
Height	38 mm	Height (inches)	1.496 inch
Width	10 mm	Width (inches)	0.394 inch
Diameter	10.3 mm	Net weight	1 g

Temperatures

Storage temperature	-40°C ... 90°C	Operating temperature range	-40°C ... 80°C
---------------------	----------------	-----------------------------	----------------

Fuse cartridge

Fuse-link standard	IEC 60269-1, IEC 60269-6, gPV (EN 60269-6)	Current	1 A
Rated DC voltage	1,000 V	Rated breaking capacity	30 kA
Contact material	silver-plated	Power dissipation, max.	0.76 W

Classifications

ETIM 7.0	EC002704	ETIM 8.0	EC002704
ETIM 9.0	EC002704	ECLASS 11.0	27-14-20-02
ECLASS 12.0	27-14-20-02	ECLASS 13.0	27-14-20-02

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	CE-Declaration_10x38_gPV_Fuses
Catalogues	Catalogues in PDF-format

FUSE 10X38 1A 1000 VDC GPV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Graph



T-I characteristic curve

FUSE 10X38 1A 1000 VDC GPV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

DC generator combiner boxes with fuses



PV Next combiner boxes for inverters with 1 to 12 MPP trackers are used to protect the DC side of a photovoltaic system. The combiner boxes protect the inverter against overvoltages and thus comply with the European Directive EN 51543-32. In addition, these products offer the possibility to protect the system against reverse currents and the possibility to combine strings to save cables during installation.

General ordering data

Type	PVN DC 3IF 30 1MPP SW S ...	Version
Order No.	2683050000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 3 Inputs / 3
GTIN (EAN)	4050118699869	Outputs per MPP, With fuse holder, Surge protection I / II, Switch
Qty.	1 pc(s).	disconnecter, Cable gland
Type	PVN DC 3IF 30 2MPP SPD1 ...	Version
Order No.	2683080000	Photovoltaics, Combiner Box, 1000 V, 2 MPP's, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118699913	per MPP, With fuse holder, Surge protection I / II, WM4C
Qty.	1 pc(s).	
Type	PVN1M2I6SXF3V201TXPX10	Version
Order No.	2683280000	Photovoltaics, Combiner Box, 1000 V, 2 MPP's, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118700169	per MPP, With fuse holder, Surge protection II, WM4C
Qty.	1 pc(s).	
Type	PVN1M1I6S0F3V000TXPX10	Version
Order No.	2737550000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 6 Inputs / 6 Outputs
GTIN (EAN)	4050118824858	per MPP, With fuse holder, Surge protection II, Switch disconnecter,
Qty.	1 pc(s).	Cable gland
Type	PVN1M1I3S0F3V201TXPX10	Version
Order No.	2683290000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118699982	per MPP, With fuse holder, Surge protection II, Switch disconnecter,
Qty.	1 pc(s).	WM4C
Type	PVN1M1I3SXF3V201TXPX10	Version
Order No.	2683270000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118700176	per MPP, With fuse holder, Surge protection II, WM4C
Qty.	1 pc(s).	
Type	PVN1M1I6SXF3V101TXPX10	Version
Order No.	2737440000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 6 Inputs / 6 Outputs
GTIN (EAN)	4032248395545	per MPP, With fuse holder, Surge protection I / II, WM4C
Qty.	1 pc(s).	
Type	PVN DC 3IF 30 1MPP SPD1 ...	Version
Order No.	2683070000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118700053	per MPP, With fuse holder, Surge protection I / II, WM4C
Qty.	1 pc(s).	
Type	PVN DC 3IF 30 2MPP SW S ...	Version
Order No.	2683060000	Photovoltaics, Combiner Box, 1000 V, 2 MPP's, 3 Inputs / 3
GTIN (EAN)	4050118699883	Outputs per MPP, With fuse holder, Surge protection I / II, Switch
Qty.	1 pc(s).	disconnecter, Cable gland
Type	PVN1M1I6SXF3V001TXPX10	Version
Order No.	2737490000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 6 Inputs / 6 Outputs
GTIN (EAN)	4050118824827	per MPP, With fuse holder, Surge protection II, WM4C
Qty.	1 pc(s).	

FUSE 10X38 1A 1000 VDC GPV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	PVN1M1I6SXF3V1O0TXPX10	Version
Order No.	2737520000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 6 Inputs / 6 Outputs
GTIN (EAN)	4050118004595	per MPP, With fuse holder, Surge protection I / II, Cable gland
Qty.	1 pc(s).	
Type	PVN1M1I6SOF3V001TXPX10	Version
Order No.	2737500000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 6 Inputs / 6 Outputs
GTIN (EAN)	4050118824834	per MPP, With fuse holder, Surge protection II, Switch disconnecter, WM4C
Qty.	1 pc(s).	
Type	PVN1M1I3SOF3V2O0TXPX10	Version
Order No.	2683250000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118700183	per MPP, With fuse holder, Surge protection II, Switch disconnecter, Cable gland
Qty.	1 pc(s).	
Type	PVN1M2I6SXF3V2O0TXPX10	Version
Order No.	2683240000	Photovoltaics, Combiner Box, 1000 V, 2 MPP's, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118700091	per MPP, With fuse holder, Surge protection II, Cable gland
Qty.	1 pc(s).	
Type	PVN DC 3IF 3O 1MPP SW S ...	Version
Order No.	2683090000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 3 Inputs / 3
GTIN (EAN)	4050118699906	Outputs per MPP, With fuse holder, Surge protection I / II, Switch disconnecter, WM4C
Qty.	1 pc(s).	
Type	PVN1M1I3SXF3V2O0TXPX10	Version
Order No.	2683230000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118699975	per MPP, With fuse holder, Surge protection II, Cable gland
Qty.	1 pc(s).	
Type	PVN1M2I6SOF3V2O0TXPX10	Version
Order No.	2683260000	Photovoltaics, Combiner Box, 1000 V, 2 MPP's, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118699968	per MPP, With fuse holder, Surge protection II, Switch disconnecter, Cable gland
Qty.	1 pc(s).	
Type	PVN1M1I6SXF3V000TXPX10	Version
Order No.	2737540000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 6 Inputs / 6 Outputs
GTIN (EAN)	4050118824841	per MPP, With fuse holder, Surge protection II, Cable gland
Qty.	1 pc(s).	
Type	PVN DC 3IF 3O 2MPP SPD 1 ...	Version
Order No.	2683040000	Photovoltaics, Combiner Box, 1000 V, 2 MPP's, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118699715	per MPP, With fuse holder, Surge protection I / II, Cable gland
Qty.	1 pc(s).	
Type	PVN DC 3IF 3O 1MPP SPD 1 ...	Version
Order No.	2683030000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118699852	per MPP, With fuse holder, Surge protection I / II, Cable gland
Qty.	1 pc(s).	
Type	PVN DC 3IF 3O 2MPP SW S ...	Version
Order No.	2683100000	Photovoltaics, Combiner Box, 1000 V, 2 MPP's, 3 Inputs / 3
GTIN (EAN)	4050118699951	Outputs per MPP, With fuse holder, Surge protection I / II, Switch disconnecter, WM4C
Qty.	1 pc(s).	
Type	PVN1M2I6SOF3V2O1TXPX10	Version
Order No.	2683300000	Photovoltaics, Combiner Box, 1000 V, 2 MPP's, 3 Inputs / 3 Outputs
GTIN (EAN)	4050118699999	per MPP, With fuse holder, Surge protection II, Switch disconnecter, WM4C
Qty.	1 pc(s).	
Type	PVN1M1I6SOF3V1O0TXPX10	Version
Order No.	2737530000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 6 Inputs / 6
GTIN (EAN)	4032248395552	Outputs per MPP, With fuse holder, Surge protection I / II, Switch disconnecter, Cable gland
Qty.	1 pc(s).	

Creation date April 28, 2024 12:46:21 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

FUSE 10X38 1A 1000 VDC GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	PVN1M1I6S0F3V1O1TXPX10	Version
Order No.	2737480000	Photovoltaics, Combiner Box, 1000 V, 1 MPP, 6 Inputs / 6
GTIN (EAN)	4032248395538	Outputs per MPP, With fuse holder, Surge protection I / II, Switch
Qty.	1 pc(s).	disconnecter, WM4C