

CA 100 DUO S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

| | |
|------------|--|
| Version | Automatic machines, Automatic stripper and crimper |
| Order No. | 2912430000 |
| Type | CA 100 DUO S |
| GTIN (EAN) | 4099986536005 |
| Qty. | 1 pc(s). |

CA 100 DUO S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 550 mm | Depth (inches) | 21.653 inch |
| Height | 440 mm | Height (inches) | 17.323 inch |
| Width | 415 mm | Width (inches) | 16.339 inch |
| Net weight | 42,000 g | | |

PW65 maintenance - automatic stripping/crimping

| | | | |
|---------------------------------------|--------------------|---------------------------------------|--|
| Compressed-air connection | 5 - 5.5 bar | Consumables | with plastic collar |
| Crimping | Trapezoidal | Crimping length | 6 - 18 mm |
| Crimping range, max. | 10 mm ² | Crimping range, min. | 4 mm ² |
| Drive | Electropneumatic | Electrical connection | 100-240 V / 50/60 Hz / 100 VA |
| Pulse time | approx. 3 s | Stripping range | 4 - 6 mm ² (10 mm ² opt.) / AWG 12-10 (AWG 8 opt.) |
| Wire end ferrules cross-section, max. | 10 mm ² | Wire end ferrules cross-section, min. | 4 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002778 | ETIM 7.0 | EC002778 |
| ETIM 8.0 | EC002778 | ETIM 9.0 | EC002778 |
| ECLASS 9.0 | 17-13-01-01 | ECLASS 9.1 | 17-13-01-01 |
| ECLASS 10.0 | 17-13-01-01 | ECLASS 11.0 | 17-13-01-01 |
| ECLASS 12.0 | 17-13-01-01 | ECLASS 13.0 | 17-13-01-01 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|