

WIRE PROCESSING CENTER FEEDER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Automated cable assembly with maximum flexibility –
Wire Processing Center (WPC)

- Modular adaptation of the system for customer-specific requirements: CUTFIX PRO, CUTFIX PRO FEEDER, CRIMPFIX R VARIO, CA 100 DUO or THM MultiMark
- Holistic assembly process including cable feeding and bundling
- Software with one-piece-flow approach for high process reliability and quality

General ordering data

Version	Automatic machines
Order No.	2816420000
Type	WIRE PROCESSING CENTER FEEDER
GTIN (EAN)	4064675312925
Qty.	1 pc(s).

WIRE PROCESSING CENTER FEEDER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	750 mm	Depth (inches)	29.528 inch
Height	1,800 mm	Height (inches)	70.866 inch
Width	1,100 mm	Width (inches)	43.307 inch
Net weight	160,820 g		

Labelling systems

Software	for data exchanging with IBM-compatible PC
----------	--

PW65 maintenance - automatic stripping/crimping

Drive	electrical	Electrical connection	100 - 240 V AC / 50/60 Hz
-------	------------	-----------------------	---------------------------

Automatic cutting

Amount pre-selection, max.	Adjustable part quantity code	Aperture (max. diameter)	8 mm outer diameter
Connected load	0.1 kW	Display	LCD display
Drive	electrical	Electrical connection	100 - 240 V AC / 50/60 Hz
Flexible/solid individual conductors	max. 10 mm ² / max. 2.5 mm ²	Keyboard	Touch display
Length pre-selection, max.	999.999 mm	Length pre-selection, min.	1 mm
Software	for data exchanging with IBM-compatible PC		

WPC

Electrical connection	100 - 240 V AC / 50/60 Hz
-----------------------	---------------------------

Classifications

ETIM 6.0	EC002224	ETIM 7.0	EC011808
ETIM 8.0	EC011808	ETIM 9.0	EC011808
ECLASS 9.0	17-13-01-90	ECLASS 9.1	17-13-01-90
ECLASS 10.0	17-13-01-90	ECLASS 11.0	17-13-01-90
ECLASS 12.0	17-13-01-90	ECLASS 13.0	17-13-01-90

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--