

**EL KSM 8.8 MM WS 30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**MultiMark MultiFit**

For connectors from competitors.

The elastic surface finish makes for simple installation.

This special material enables the strips to be stretched to accommodate slight variations in spacing, especially with long terminal blocks.

A print resolution of 300 dpi also produces a very legible script.

**Your benefits with MultiMark**

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence
- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

**General ordering data**

Version	Terminal marker, Pitch in mm (P): 8.80 white
Order No.	<a href="#">2922670000</a>
Type	EL KSM 8.8 MM WS 30M
GTIN (EAN)	4099986618275
Qty.	1 pc(s).

- Firm hold and durable printing
- Continuous strips save installation time

**EL KSM 8.8 MM WS 30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.25 mm	Depth (inches)	0.01 inch
Length	30 m	Length (inches)	1,181.102 inch
Net weight	280 g		

**General data**

Colour	white	Halogen	No
Length	30 m	Material	Polypropylene
Operating temperature range, max.	90 °C	Operating temperature range, min.	-50 °C
Printing method	Thermal transfer	Type of printing	neutral
UL 94 flammability rating	V-2		

**Connector markers**

Pitch in mm (P)	8.8 mm
-----------------	--------

**Classifications**

ETIM 6.0	EC000761	ETIM 7.0	EC000761
ETIM 8.0	EC000761	ETIM 9.0	EC000761
ECLASS 9.0	27-14-11-37	ECLASS 9.1	27-14-11-37
ECLASS 10.0	27-14-11-37	ECLASS 11.0	27-28-11-01
ECLASS 12.0	27-28-11-01	ECLASS 13.0	27-28-11-01

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

### EL KSM 8.8 MM WS 30M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

