

**SIHA 3/G20/LD 60-150V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

**General ordering data**

Version	Fuse holder for feed-through modular terminal, 2.31 mA, pluggable
Order No.	<a href="#">7921590000</a>
Type	SIHA 3/G20/LD 60-150V
GTIN (EAN)	4032248322626
Qty.	25 pc(s).

## SIHA 3/G20/LD 60-150V

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	63.1 mm	Depth (inches)	2.484 inch
Height	39.38 mm	Height (inches)	1.55 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	8.48 g		

## Temperatures

Operating temperature	-50 °C...120	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

## Material data

Material	Wemid	Insulating material	Wemid
Colour	black	UL 94 flammability rating	V-0

## System specifications

Version	Fuse cartridge	End cover plate required	No
---------	----------------	--------------------------	----

## Additional technical data

Installation advice	Operating instructions/catalogue	Type of mounting	Plugged
---------------------	----------------------------------	------------------	---------

## Conductors for clamping (rated connection)

Type of connection	Plug-in connection
--------------------	--------------------

## General

Installation advice	Operating instructions/catalogue	Operating temperature range, max.	120 °C
---------------------	----------------------------------	-----------------------------------	--------

## Rating data

Rated voltage	250 V	Rated impulse withstand voltage	4 kV
Pollution severity	3		

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

## Approvals

ROHS	Conform
------	---------

## SIHA 3/G20/LD 60-150V

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
Product Change Notification	<a href="#">PCN - EN</a> <a href="#">PCN - DE</a>
User Documentation	<a href="#">Beipackzettel_SIHA3.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## SIHA 3/G20/LD 60-150V

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

