

SIHA 3/G20/LD 35-70V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

General ordering data

Version	Fuse holder for feed-through modular terminal, 2.31 mA, pluggable
Order No.	7921580000
Type	SIHA 3/G20/LD 35-70V
GTIN (EAN)	4032248322619
Qty.	25 pc(s).

SIHA 3/G20/LD 35-70V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	63.1 mm	Depth (inches)	2.484 inch
Height	39.38 mm	Height (inches)	1.55 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	7.04 g		

Temperatures

Operating temperature	-50 °C...120	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Insulating material	Wemid
Colour	black	UL 94 flammability rating	V-0

System specifications

Version	Fuse cartridge	End cover plate required	No
---------	----------------	--------------------------	----

Additional technical data

Installation advice	Operating instructions/catalogue	Type of mounting	Plugged
---------------------	----------------------------------	------------------	---------

Conductors for clamping (rated connection)

Type of connection	Plug-in connection
--------------------	--------------------

General

Installation advice	Operating instructions/catalogue	Operating temperature range, max.	120 °C
---------------------	----------------------------------	-----------------------------------	--------

Rating data

Rated voltage	250 V	Rated impulse withstand voltage	4 kV
Pollution severity	3		

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Approvals

ROHS	Conform
------	---------

SIHA 3/G20/LD 35-70V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
Product Change Notification	PCN - EN PCN - DE
User Documentation	Beipackzettel_SIHA3.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

SIHA 3/G20/LD 35-70V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

