

KEBIQL303015S2N0 AL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The new Klippon® EBi enclosure series has been specially designed for use in industrial environments. It reliably meets all requirements for use in harsh environments and is characterised by attractive performance features. The cost-effective stainless steel enclosures allow a very economical calculation and are also suitable for projects with a limited budget. In addition to Klippon® EBi for industrial applications, there is Klippon® EBx for hazardous areas. Enclosures with cULus approvals are available on request.

General ordering data

Version	Klippon EBi QL (Essential Box industrial - Quarter Lock), Enclosures, Height: 300 mm, Width: 300 mm, Depth: 150 mm, Material: Stainless steel 1.4301 (304), untreated, silver
Order No.	8000090357
Type	KEBIQL303015S2N0 AL
GTIN (EAN)	4064675855705
Qty.	1 pc(s).

KEBIQL303015S2N0 AL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	150 mm	Depth (inches)	5.905 inch
Height	300 mm	Height (inches)	11.811 inch
Width	300 mm	Width (inches)	11.811 inch
Net weight	4,900 g		

Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

General information

Enclosure attachment	Installation through the housing rear wall	Flange plate	No
Impact resistance	10 J version standard	Lid attachment	Quarter-turn fastener with double-bit insert
Material	Stainless steel 1.4301 (304)	Material thickness of cover	1.5 mm
Material thickness of enclosure	1.5 mm	Note: protection class	IP protection is only given after wall mounting using the enclosed sealing washers.
Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
Protection degree	IP66	Seal material	Chloroprene
Silicone	No	Surface finish	untreated

Classifications

ETIM 6.0	EC000261	ETIM 7.0	EC000261
ETIM 8.0	EC000261	ETIM 9.0	EC000261
ECLASS 9.0	27-18-01-01	ECLASS 9.1	27-18-92-90
ECLASS 10.0	27-18-01-01	ECLASS 11.0	27-18-01-01
ECLASS 12.0	27-18-01-01	ECLASS 13.0	27-18-01-01

Approvals

Approvals




Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity - Klippon EBi Empty Enclosures - DoC KEBI DE PS2650 220428 001ISS00
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

KEBIQL303015S2N0 AL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

KEBIQL303015S2N0 AL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Double-bit key



With the double-bit key, the locking element of the enclosure door can be locked and opened.

General ordering data

Type	KLIPPON QL KEY	Version
Order No.	2473930000	Klippon EB (Essential Box), Key, Miscellaneous, Material: Plastic
GTIN (EAN)	4050118485868	
Qty.	5 pc(s).	

Spacer



Stainless steel spacers in three lengths to increase the distance between the mounting rails or DIN rails and the rear wall of the enclosure.

General ordering data

Type	SP M6 30 MSZN	Version
Order No.	3896300000	Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm,
GTIN (EAN)	4008190850241	Depth: 30 mm, Material: Steel, silver
Qty.	2 pc(s).	
Type	SP M6 15 MSZN	Version
Order No.	3896100000	Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm,
GTIN (EAN)	4008190857851	Depth: 15 mm, Material: Steel, silver
Qty.	2 pc(s).	
Type	SP M6 20 MSZN	Version
Order No.	3896200000	Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm,
GTIN (EAN)	4008190850234	Depth: 20 mm, Material: Steel, silver
Qty.	2 pc(s).	

KEBIQL303015S2N0 AL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Mounting feet**

With the additionally available mounting feet, the enclosures can also be mounted from outside the enclosure.

General ordering data

Type	KEB MOFT SMALL S4 SET	Version
Order No.	2660200318	Klippon EB (Essential Box), Mounting foot, Height: 38 mm, Width: 55
GTIN (EAN)	4064675275695	mm, Depth: 10.5 mm, Material: Steel, untreated, silver
Qty.	1 pc(s).	

Document holders

Document holders for the proper storage of documents in the enclosure.

General ordering data

Type	DOHA KEB A6 S4B R	Version
Order No.	8000075807	Klippon EB (Essential Box), Enclosures, Riveted, Height: 95 mm, Depth:
GTIN (EAN)	4064675425359	20 mm, Material: Stainless steel 1.4404, silver
Qty.	1 pc(s).	

KEBIQL303015S2N0 AL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type label holder



There are a variety of designed label holders available for prominent display as required and for additional nameplates as needed.

General ordering data

Type	TPSDHA KEB 100X25 S4B R	Version
Order No.	8000075818	Klippon EB (Essential Box), Enclosures, Riveted, Height: 25 mm, Width:
GTIN (EAN)	4064675425632	141 mm, Depth: 16.5 mm, Material: Stainless steel 1.4404 (316L),
Qty.	1 pc(s).	Brushed, silver
Type	TPSDHA KEB 130X50 S4B R	Version
Order No.	8000075816	Klippon EB (Essential Box), Enclosures, Riveted, Height: 50 mm, Width:
GTIN (EAN)	4064675425366	171 mm, Depth: 16.5 mm, Material: Stainless steel 1.4404 (316L),
Qty.	1 pc(s).	Brushed, silver

Installation material

**Integrate, expand and customise - the perfect supplement to every application**

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

Mounting hardware kits

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The **label fastening set – SD** is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The **universal fastening set – TPSD** has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

General ordering data

Type	LKSC M6X8 A2 TX30	Version
Order No.	2704960000	Klippon TB (Terminal Box), Set of fixings, Height: 11.3 mm, Width:
GTIN (EAN)	4050118753196	13.6 mm, Depth: 13.6 mm, Material: Stainless steel, rust-proof,
Qty.	500 pc(s).	untreated, silver

KEBIQL303015S2N0 AL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Mounting plates**

Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

General ordering data

Type	KEB MOPL 3030 S2N H	Version
Order No.	8000074316	Klippon EB (Essential Box), Mounting plate, Height: 240 mm, Width:
GTIN (EAN)	4064675425267	240 mm, Depth: 1.5 mm, Material: Stainless steel 1.4301 (304),
Qty.	1 pc(s).	untreated, silver
Type	KEB MOPL 3030 MSZN	Version
Order No.	8000074171	Klippon EB (Essential Box), Mounting plate, Height: 240 mm, Width:
GTIN (EAN)	4064675425168	240 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, silver
Qty.	1 pc(s).	
Type	GFSC M5X10 TX20 SET	Version
Order No.	1274150000	Klippon EB (Essential Box), Mounting screw, Height: 13.3 mm, Width:
GTIN (EAN)	4050118063820	8.5 mm, Depth: 8.5 mm, Material: Steel, galvanized, galvanic zinc
Qty.	1 pc(s).	plated and passivated, silver