

IE-CCM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Weidmüller connecting module is helpful whenever you have to repair or want to extend a broken installation cable without cable reserve in confined spaces.

General ordering data

Version	Connecting module, Cat.7 (ISO/IEC 11801), IP20
Order No.	8808410000
Type	IE-CCM
GTIN (EAN)	4032248505999
Qty.	1 pc(s).

IE-CCM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	20 mm	Height (inches)	0.787 inch
Width	37 mm	Width (inches)	1.457 inch
Length	112 mm	Length (inches)	4.409 inch
Net weight	155 g		

General Info

Connection 1	IDC	Connection 2	IDC
Description of article	Connecting module	Colour	grey
Housing main material	fully shielded metal housing	Category	Cat.7 (ISO/IEC 11801)
Sheath diameter, min.	5.5 mm	Sheath diameter, max.	9.6 mm
Type of mounting		Shielding	Captive 360° shield connection with separate strain relief
	Wall mounting		
Protection degree	IP20		

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ETIM 9.0	EC002780
ECLASS 9.0	27-14-11-52	ECLASS 9.1	27-14-11-52
ECLASS 10.0	27-14-11-52	ECLASS 11.0	27-14-11-52
ECLASS 12.0	27-14-11-52	ECLASS 13.0	27-14-11-52

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN

IE-CCM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Indentation tool for twisted-pair cables****Indentation tool for twisted-pair cables**

A variety of blades for terminal strips

- of type 110 from AT&T
- type 66,
- type LSA Plus from Krone (standard and scissors-type cutting action), also for 630A6 telephone sockets

General ordering data

Type	PUNCH DOWN TOOL PDT	Version
Order No.	9013970000	Accessories, Crimping tool for contacts
GTIN (EAN)	4008190887957	
Qty.	1 pc(s).	