

Y-INTERFACE BLL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Pluggable energy distributors

Pluggable double connection for power distribution and supply of devices

- 2-pin, color-coded
- 230 V, IP 30

General ordering data

Order No.	8000075197
Type	Y-INTERFACE BLL
GTIN (EAN)	8430243428422
Qty.	16 pc(s).

Y-INTERFACE BLL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	16.4 mm	Depth (inches)	0.646 inch
Height	38.4 mm	Height (inches)	1.512 inch
Width	15.2 mm	Width (inches)	0.598 inch
Net weight	7.4 g		

Temperatures

Storage temperature	-40...70 °C	Operating temperature	-40...70 °C
Humidity at operating temperature	0...85% (no condensation)		

Connection data

Distribution PCB connectors	LSF-SMT 5.08/03/180 (no central pin)	Supply plug-in connectors	BLL 5.08/03/90 (no central pin)
-----------------------------	---	---------------------------	---------------------------------

Rating data

Protection degree	IP30	Operating voltage	230 V
Maximum current per distributor connection	6 A	Total operating current	12 A

Insulation coordination (EN 60664-1)

Rated insulation voltage	250 V AC	Surge voltage category	III
Pollution severity	3	Pulse voltage test (1,2/50 µs)	6 kV

Connection field

Clamping range, max.	1.5 mm ²	Clamping range, min.	0.13 mm ²
Max. wire cross-section, AWG	AWG 14	Min. wire cross-section, AWG	AWG 28
Stripping length	10 mm	Type of connection	PUSH IN

Supply connection

Type of connection	Plug-in connection
--------------------	--------------------

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ETIM 9.0	EC002780
ECLASS 9.0	27-14-11-52	ECLASS 9.1	27-14-11-52
ECLASS 10.0	27-14-11-52	ECLASS 11.0	27-14-11-52
ECLASS 12.0	27-14-11-52	ECLASS 13.0	27-14-11-52

Approvals

Approvals



ROHS

Conform

Y-INTERFACE BLL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity

[EU Declaration of conformity](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[EN Data Sheet](#)

[DE Data Sheet](#)

Catalogues

[Catalogues in PDF-format](#)

Y-INTERFACE BLL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings**