

STRIPAX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

| | |
|------------|-----------------------------------|
| Version | Tools, Stripping and cutting tool |
| Order No. | 9005000000 |
| Type | STRIPAX |
| GTIN (EAN) | 4008190072506 |
| Qty. | 1 pc(s). |

STRIPAX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|----------|-----------------|------------|
| Depth | 22 mm | Depth (inches) | 0.866 inch |
| Height | 99 mm | Height (inches) | 3.898 inch |
| Width | 190 mm | Width (inches) | 7.48 inch |
| Net weight | 174.63 g | | |

Technical data

| | |
|------------------------|---|
| Description of article | Stripping tool for up to 10 mm ² |
|------------------------|---|

Stripping tools

| | | | |
|-------------------------------|---|--|----------------------|
| Cable type | Flexible and solid conductors with PVC insulation | Conductor cross-section (cutting capacity) | 6 mm ² |
| Conductor cross-section, max. | 10 mm ² | Conductor cross-section, min. | 0.08 mm ² |
| Stripping length, max. | 25 mm | Stripping range AWG, max. | 8 AWG |
| Stripping range AWG, min. | 28 AWG | Stripping range, min. | 0.08 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002109 | ETIM 7.0 | EC002109 |
| ETIM 8.0 | EC002109 | ETIM 9.0 | EC002109 |
| ECLASS 9.0 | 21-04-37-06 | ECLASS 9.1 | 21-04-37-06 |
| ECLASS 10.0 | 21-04-37-06 | ECLASS 11.0 | 21-04-37-06 |
| ECLASS 12.0 | 21-04-37-06 | ECLASS 13.0 | 21-04-37-06 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0 |

Downloads

| | |
|-----------------------------|---|
| Engineering Data | CAD data – STEP |
| Product Change Notification | Technische Änderung für Abisolierwerkzeug Stripax Technical change to stripping tool Stripax |
| User Documentation | Manual Library and function block – BDAL Stripax all version |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

STRIPAX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



STRIPAX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Accessories / replacement parts



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

| | | |
|------------|----------------------------|---------------------------------------|
| Type | ERME 10 ² SPX 4 | Version |
| Order No. | 1119030000 | Accessories, Cutter holder |
| GTIN (EAN) | 4032248948420 | |
| Qty. | 1 pc(s). | |
| Type | ERTE BAGR AN KP SPX 4 | Version |
| Order No. | 2905400000 | Accessories, Replacement clamping jaw |
| GTIN (EAN) | 4099986551381 | |
| Qty. | 1 pc(s). | |
| Type | ERTE KLBC SPX 10 | Version |
| Order No. | 2571480000 | Accessories, Replacement clamping jaw |
| GTIN (EAN) | 4050118582109 | |
| Qty. | 1 pc(s). | |