

TS35X15 ST KTB9176 HOR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Similar to illustration

General ordering data

Version	Klippon TB (Terminal Box), Enclosures, without slot, Height: 35 mm, Width: 689 mm, Depth: 15 mm, Material: Steel, galvanic zinc plated and passivated, silver
Order No.	8000116377
Type	TS35X15 ST KTB9176 HOR
GTIN (EAN)	4099986820852
Qty.	20 pc(s).

TS35X15 ST KTB9176 HOR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	15 mm	Depth (inches)	0.591 inch
Height	35 mm	Height (inches)	1.378 inch
Width	689 mm	Width (inches)	27.126 inch
Net weight	481.88 g		

General information

Installation advice	Direct mounting	Integral fixing	Screwed
Material	Steel	Standards	DIN EN 60715
Surface finish	galvanic zinc plated and passivated		

General information on accessories

Material	Steel	Surface finish	galvanic zinc plated and passivated
----------	-------	----------------	-------------------------------------

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

TS35X15 ST KTB9176 HOR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Mounting plates



Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

General ordering data

Type	GFSC M5X10 TX20 SET	Version
Order No.	1274150000	Klippon EB (Essential Box), Mounting screw, Height: 13.3 mm, Width:
GTIN (EAN)	4050118063820	8.5 mm, Depth: 8.5 mm, Material: Steel, galvanized, galvanic zinc
Qty.	1 pc(s).	plated and passivated, silver