

H2,5/17,5X BL SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- supplied loose in polybag
- Weidmüller colour code

General ordering data

| | |
|------------|---|
| Version | Wire-end ferrule, Standard, 14 mm, 8 mm, blue |
| Order No. | 9006670000 |
| Type | H2,5/17,5X BL SV |
| GTIN (EAN) | 4008190332273 |
| Qty. | 100 pc(s). |
| Packaging | Multipack bag |

H2,5/17,5X BL SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | |
|------------|--------|
| Net weight | 0.25 g |
|------------|--------|

Technical data

| | | | |
|------------------------|--|---------|----------|
| Description of article | Wire end ferrule for short-circuit-proof and earth-fault-proof lines, blue | Version | Standard |
|------------------------|--|---------|----------|

Wire-end ferrules

| | | | |
|-----------------------------|---------------------|---|-------------|
| Collar diameter (D2) | 7.6 mm | Colour code | Weidmueller |
| Conductor cross-section | 2.5 mm ² | Contact surface diameter (D1) | 2.3 mm |
| Contact surface length (L2) | 8 mm | L1 in mm | 17.5 mm |
| Metal sleeve thickness (S1) | 0.15 mm | Plastic collar thickness (S2) | 0.3 mm |
| Stripping length | 14 mm | Wire connection cross section AWG, max. | AWG 14 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ECLASS 9.0 | 27-40-02-01 | ECLASS 9.1 | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

H2,5/17,5X BL SV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

