

IE-S-IP67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Junction box, design for SnapIn plug-in connectors ver.6
according to IEC 61076-3-106, plastic

General ordering data

Version	Connecting plug, Junction box, IP67, Cat.6A / Class E _A (ISO/IEC 11801 2010), Variant 6 to IEC 61076-3-106
Order No.	8808370000
Type	IE-S-IP67
GTIN (EAN)	403224850595 1
Qty.	1 pc(s).

IE-S-IP67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	90 g
------------	------

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

General data

Colour	Configuration	Screw-on junction box including RJ45 module with IDC connection
	Light Grey	
Housing main material	PA 66, UL 94: V-0	Plugging cycles
Protection degree		750
	IP67	Type of mounting
		Floor-mounted, for exposed connections, Wall mounting
Wiring	EIA/TIA T568 A, EIA/TIA T568 B	

General standards

Certificate No. (DNV)	TAE00003EW	Connector standard	IEC 61076-3-106 Var. 6
-----------------------	------------	--------------------	------------------------

Technical data RJ45 module

Wiring	EIA/TIA T568 A, EIA/TIA T568 B
--------	--------------------------------

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-44-03-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-44-03-90	ECLASS 13.0	27-44-03-90

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity

[GOST Approval](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[MAN IE GUIDE DE](#)
[MAN IE GUIDE EN](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)
[PI PROFINET CABLING EN](#)
[PI PROFINET CABLING EN](#)

Creation date May 11, 2024 12:33:04 PM CEST

Catalogue status 04.05.2024 / We reserve the right to make technical changes.

IE-S-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



IE-S-IP67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Sets - RJ45**

SnapIn plug-in connectors according to IEC 61076-3-106 ver.6 in plastic, with RJ45 insert

**General ordering data**

Type	IE-P-IP67	Version
Order No.	8808380000	Connecting plug, Plug, IP67, Cat.6A / Class E _A (ISO/IEC 11801
GTIN (EAN)	4032248505968	2010), Variant 6 to IEC 61076-3-106
Qty.	1 pc(s).	

... for modular plug-in connectors**Crimping tools for modular plug-in connector systems WE and DEC**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Three functions in one tool

General ordering data

Type	TT 8 RS MP 8	Version
Order No.	9202800000	Pressing tools, Crimping tool for contacts
GTIN (EAN)	4032248512072	
Qty.	1 pc(s).	