

**DMS 3 SET 1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

**General ordering data**

Version	DMS 3, Mains-operated torque screwdriver
Order No.	<a href="#">9007470000</a>
Type	DMS 3 SET 1
GTIN (EAN)	4008190299224
Qty.	1 pc(s).

**DMS 3 SET 1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	205 mm	Depth (inches)	8.071 inch
Width	325 mm	Width (inches)	12.795 inch
Net weight	1,770 g		

**Technical data**

Description of article	Cordless torque screwdriver set, incl. rechargeable battery, charger, bits, plastic case
------------------------	--

**Electric screwdriver**

Battery voltage	2.4 V	Bit holder	1/4" DIN 3126 Form E6.3
Idling speed	200 u. 400 min <sup>-1</sup>	Rated voltage	2.4 V
Rechargeable batteries	Ni-Mh cells	Torque setting, max.	3 Nm
Torque setting, min.	0.3 Nm	Weight	2,004 g
Weight of rechargeable battery	122 g		

**Screwing tools**

Torque setting, max.	3 Nm	Torque setting, min.	0.3 Nm
----------------------	------	----------------------	--------

**Classifications**

ETIM 6.0	EC001395	ETIM 7.0	EC001395
ETIM 8.0	EC001395	ETIM 9.0	EC001395
ECLASS 9.0	21-05-21-90	ECLASS 9.1	21-04-04-17
ECLASS 10.0	21-05-21-90	ECLASS 11.0	21-05-08-90
ECLASS 12.0	21-05-08-90	ECLASS 13.0	21-05-08-90

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	8a39b146-a7e9-4fe1-a2bc-f82c0bb3aeeb

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

### DMS 3 SET 1

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use



## DMS 3 SET 1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## E6.3 bits - Phillips / recess

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
Crosshead bits are Phillips-Recessed type PH/DIN 5260.  
1/4" drive, E6.3 DIN 3126



## General ordering data

Type	BIT E6,3 PH1X70	Version
Order No.	<a href="#">9024080000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870744	
Qty.	5 pc(s).	
Type	BIT E6,3 PH2X70	Version
Order No.	<a href="#">9024090000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870720	
Qty.	5 pc(s).	

## E6.3 bits - Pozidriv / Supadriv

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
Crosshead bits Pozidriv PZ/DIN 5262, 1/4" drive, E 6.3  
DIN 3126



## General ordering data

Type	BIT E6,3 PZ1X70	Version
Order No.	<a href="#">9024100000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870713	
Qty.	5 pc(s).	
Type	BIT E6,3 PZ2X70	Version
Order No.	<a href="#">9024110000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870706	
Qty.	5 pc(s).	

**DMS 3 SET 1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Bit assortment, E6.3**

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

**General ordering data**

Type	BIT-BOX WI DMS 3	Version
Order No.	<a href="#">9024970000</a>	Accessories, Mounting tool
GTIN (EAN)	4032248068067	
Qty.	1 pc(s).	

**DMS 3**

Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

**General ordering data**

Type	AKKU DMS 3	Version
Order No.	<a href="#">9007450000</a>	DMS 3, Battery
GTIN (EAN)	4008190450106	
Qty.	1 pc(s).	

## DMS 3 SET 1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## BE6.3 bits - slotted

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126



## General ordering data

Type	BIT E6,3 0,6X3,5X70	Version
Order No.	<a href="#">9024020000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852627	
Qty.	5 pc(s).	
Type	BIT E6,3 0,5X3,0X70	Version
Order No.	<a href="#">9024000000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852634	
Qty.	5 pc(s).	
Type	BIT E6,3 0,8X4,0X70	Version
Order No.	<a href="#">9024030000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852658	
Qty.	5 pc(s).	
Type	BIT E6,3 0,4X2,5X70	Version
Order No.	<a href="#">9020750000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4032248504725	
Qty.	5 pc(s).	
Type	BIT E6,3 Z 0,8X4,0X39	Version
Order No.	<a href="#">9025590000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190151935	
Qty.	10 pc(s).	
Type	BIT E6,3 1,0X5,5X70	Version
Order No.	<a href="#">9024040000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852665	
Qty.	5 pc(s).	
Type	BIT E6,3 1,2X6,5X70	Version
Order No.	<a href="#">9020740000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4032248504718	
Qty.	5 pc(s).	

**DMS 3 SET 1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****DMS PRO**

Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

**General ordering data**

Type	LG DMS PRO/ DMS 3	Version
Order No.	<a href="#">9007460000</a>	DMS 3, 90 % bei 3x 500 V AC / > 91 % bei 3 x 400 V AC
GTIN (EAN)	4008190404970	
Qty.	1 pc(s).	