


H10,0/26T ZH BR SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- in multipack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Twin wire-end ferrule, 17 mm, 12 mm, brown |
| Order No. | 9005170000 |
| Type | H10,0/26T ZH BR SV |
| GTIN (EAN) | 4008190482756 |
| Qty. | 100 pc(s). |
| Packaging | Multipack bag |

H10,0/26T ZH BR SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | |
|------------|--------|
| Net weight | 0.89 g |
|------------|--------|

Technical data

| | | | |
|------------------------|------------------------------|---------|-----------------------|
| Description of article | Twin wire end ferrule, brown | Version | Twin wire-end ferrule |
|------------------------|------------------------------|---------|-----------------------|

Wire-end ferrules

| | | | |
|---|---------------|-----------------------------|--------------------|
| Collar height (A) | 13.4 mm | Collar width (B) | 7.6 mm |
| Colour code | Telemecanique | Conductor cross-section | 10 mm ² |
| Contact surface diameter (D1) | 5.8 mm | Contact surface length (L2) | 12 mm |
| L1 in mm | 26 mm | Metal sleeve thickness (S1) | 0.2 mm |
| Plastic collar thickness (S2) | 0.5 mm | Stripping length | 17 mm |
| Wire connection cross section AWG, max. | AWG 8 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ECLASS 9.0 | 27-40-02-01 | ECLASS 9.1 | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

H10,0/26T ZH BR SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Drawing**