

CUTFIX 8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

General ordering data

Version	Cutting machine
Order No.	9023100000
Type	CUTFIX 8
GTIN (EAN)	4032248143184
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2025-01-06
Alternative product	2797190000

CUTFIX 8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	360 mm	Depth (inches)	14.173 inch
Height	470 mm	Height (inches)	18.504 inch
Width	385 mm	Width (inches)	15.157 inch
Net weight	20,289 g		

Automatic cutting

Amount pre-selection, max.	Adjustable part quantity code	Aperture (max. diameter)	8 mm outer diameter
Connected load	0.12 kW	Correction for length	Slip correction in mm can be programmed to suit the part.
Display	LCD display	Drive	electrical
Electrical connection	100 - 240 V AC / 50/60 Hz	Feeding speed, max.	1.5 m/s
Flexible/solid individual conductors	max. 10 mm ² / max. 2.5 mm ²	Interface	USB 1.1
Keyboard	Entry and functions keypad	Length pre-selection, max.	999,999 mm
Length pre-selection, min.	1 mm	Software	for data exchanging with IBM-compatible PC
Storage	Up to 200 cutting orders		

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-03
ECLASS 10.0	17-13-01-03	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

CUTFIX 8

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



CUTFIX 8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories / replacement parts**

- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

General ordering data

Type	AIMESA V CUTFIX	Version
Order No.	9054740000	Accessories, Replacement part
GTIN (EAN)	4032248104512	
Qty.	1 pc(s).	
Type	DOPPELZAHNRIEMEN VORSCH	Version
Order No.	9054750000	Automatic machines, Replacement part
GTIN (EAN)	4032248104529	
Qty.	1 pc(s).	
Type	ZAHNRIEMENVORSCHUBMOTOR	Version
Order No.	9054760000	Automatic machines, Replacement part
GTIN (EAN)	4032248104536	
Qty.	1 pc(s).	
Type	ATR CTF	Version
Order No.	1428560000	Accessories, Replacement part
GTIN (EAN)	4050118232899	
Qty.	1 pc(s).	
Type	ATM CTF	Version
Order No.	1428570000	Automatic machines, Replacement part
GTIN (EAN)	4050118232790	
Qty.	1 pc(s).	