

**PZ 16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

**General ordering data**

Version	Pressing tool, Crimping tool for wire-end ferrules, 6mm <sup>2</sup> , 16mm <sup>2</sup> , Indent crimp
Order No.	<a href="#">9012600000</a>
Type	PZ 16
GTIN (EAN)	4008190035440
Qty.	1 pc(s).
Replacement parts	<a href="#">9012640000</a> <a href="#">9202810000</a>

**PZ 16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Net weight	429.8 g		

**Technical data**

Description of article	(2)Crimping tool	Version	Mechanical, without interchangeable inserts
------------------------	------------------	---------	---

**Description of contact**

Conductor cross-section, max. AWG	AWG 6	Conductor cross-section, min. AWG	AWG 10
Crimping range, max.	16 mm <sup>2</sup>	Crimping range, min.	6 mm <sup>2</sup>
Type of contact	Wire-end ferrules with/without plastic collars		

**tool data crimping**

Crimping type/profile	Indent crimp	Wire end ferrules cross-section, max.	16 mm <sup>2</sup>
Wire end ferrules cross-section, min.	6 mm <sup>2</sup>		

**Classifications**

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">manual PZ16 PZ6/5</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## PZ 16

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

