

HTF DFF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for for turned/stamped contact**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

| | |
|------------|---|
| Version | Pressing tool, Crimping tool for contacts, 0.22mm², 2.5mm², B-Crimp |
| Order No. | 9014140000 |
| Type | HTF DFF |
| GTIN (EAN) | 4008190297305 |
| Qty. | 1 pc(s). |

HTF DFF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|--------|----------------|------------|
| Width | 205 mm | Width (inches) | 8.071 inch |
| Net weight | 442 g | | |

Technical data

| | | | |
|------------------------|--|---------|---|
| Description of article | Crimping tools for Weidmüller DFF contacts | Version | Mechanical, without interchangeable inserts |
|------------------------|--|---------|---|

Description of contact

| | | | |
|-----------------------------------|---------------------|-----------------------------------|----------------------|
| Conductor cross-section, max. AWG | AWG 14 | Conductor cross-section, min. AWG | AWG 24 |
| Crimping range, max. | 2.5 mm ² | Crimping range, min. | 0.22 mm ² |
| Type of contact | Weidmüller DFF | | |

tool data crimping

| | | | |
|---------------------------------------|----------------------|---------------------------------------|---------------------|
| Crimping type/profile | B-Crimp | Wire end ferrules cross-section, max. | 2.5 mm ² |
| Wire end ferrules cross-section, min. | 0.22 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000168 | ETIM 7.0 | EC000168 |
| ETIM 8.0 | EC000168 | ETIM 9.0 | EC000168 |
| ECLASS 9.0 | 21-04-38-11 | ECLASS 9.1 | 21-04-38-11 |
| ECLASS 10.0 | 21-04-38-11 | ECLASS 11.0 | 21-04-38-11 |
| ECLASS 12.0 | 21-04-38-11 | ECLASS 13.0 | 21-04-38-11 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 2159813b-98fd-4068-b62a-bc89a046c012 |

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | Declaration of the Manufacturer |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

HTF DFF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

