

CRIMP-SET PZ 50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 50, Stripping tool: AM 25, Crimping range, min.: 25, Colour code: Weidmüller
Order No.	9028850000
Type	CRIMP-SET PZ 50
GTIN (EAN)	403224838405 1
Qty.	1 pc(s).
Packaging	Plastic box

Creation date April 29, 2024 10:06:32 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

CRIMP-SET PZ 50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	261 mm	Depth (inches)	10.276 inch
Height	57 mm	Height (inches)	2.244 inch
Width	338 mm	Width (inches)	13.307 inch
Net weight	1,759.55 g		

Technical data

Description of article	Set includes crimping tool for up to 50 mm ² , stripping tool and wire-end ferrules in Weidmüller colour code
------------------------	--

Assortments

Colour code	Weidmüller	Crimping range, max.	50 mm ²
Crimping range, min.	25 mm ²	Crimping tool	PZ 50
Number of AEH	200 pcs.	Packaging	Plastic box
Stripping tool	AM 25		

Classifications

ETIM 6.0	EC000524	ETIM 7.0	EC000524
ETIM 8.0	EC000524	ETIM 9.0	EC000524
ECLASS 9.0	27-40-02-18	ECLASS 9.1	27-40-02-18
ECLASS 10.0	27-40-02-18	ECLASS 11.0	27-40-02-18
ECLASS 12.0	27-40-02-18	ECLASS 13.0	27-40-02-18

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

CRIMP-SET PZ 50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Crimping tools****Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 50	Version
Order No.	9006450000	Pressing tool, Crimping tool for wire-end ferrules, 25mm ² , 50mm ² ,
GTIN (EAN)	4008190095796	Indent crimp
Qty.	1 pc(s).	

Tools

Sheathing stripper for PVC cables

**General ordering data**


Type	AM 25	Version
Order No.	9001540000	Tools, Sheathing strippers
GTIN (EAN)	4008190138271	
Qty.	1 pc(s).	

CRIMP-SET PZ 50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Conductor nom. cross-section 35mm²**

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H35,0/30D 16 R	Version		Packaging	
Order No.	9019310000	Wire-end ferrule, Standard, 19 mm, 16 mm, red		loose	
GTIN (EAN)	4008190102234				
Qty.	50 pc(s).				

Conductor nom. cross-section 50mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H50,0/36D BL	Version		Packaging	
Order No.	9019340000	Wire-end ferrule, Standard, 26 mm, 20 mm, blue		loose	
GTIN (EAN)	4008190067632				
Qty.	50 pc(s).				

CRIMP-SET PZ 50

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Conductor nom. cross-section 25mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H25,0/30T SW	Version	Packaging
Order No.	9021190000	Wire-end ferrule, Standard, 18 mm, 16 mm, black	loose
GTIN (EAN)	4008190115166		
Qty.	50 pc(s).		
Type	H25,0/36T SW	Version	Packaging
Order No.	9021200000	Wire-end ferrule, Standard, 24 mm, 22 mm, black	loose
GTIN (EAN)	4008190055400		
Qty.	50 pc(s).		