

CRIMP-SET PZ 16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 16, Stripping tool: STRIPAX 16, Crimping range, min.: 6, Colour code: Weidmüller
Order No.	9025850000
Type	CRIMP-SET PZ 16
GTIN (EAN)	4008190184520
Qty.	1 pc(s).
Packaging	Plastic box

Creation date April 29, 2024 11:01:26 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

CRIMP-SET PZ 16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	261 mm	Depth (inches)	10.276 inch
Height	57 mm	Height (inches)	2.244 inch
Width	338 mm	Width (inches)	13.307 inch
Net weight	1,680.74 g		

Technical data

Description of article	Set includes crimping tool for up to 16 mm ² , stripping tool and wire-end ferrules in Weidmüller colour code
------------------------	--------------------------------------------------------------------------------------------------------------------------

Assortments

Colour code	Weidmüller	Crimping range, max.	16 mm ²
Crimping range, min.	6 mm ²	Crimping tool	PZ 16
Number of AEH	400 pcs.	Packaging	Plastic box
Stripping tool	STRIPAX 16		

Classifications

ETIM 6.0	EC000524	ETIM 7.0	EC000524
ETIM 8.0	EC000524	ETIM 9.0	EC000524
ECLASS 9.0	27-40-02-18	ECLASS 9.1	27-40-02-18
ECLASS 10.0	27-40-02-18	ECLASS 11.0	27-40-02-18
ECLASS 12.0	27-40-02-18	ECLASS 13.0	27-40-02-18

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

CRIMP-SET PZ 16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version
Order No.	9005000000	Tools, Stripping and cutting tool
GTIN (EAN)	4008190072506	
Qty.	1 pc(s).	

Inserts



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	EINSATZ A8-1 CL55	Version
Order No.	9028460000	Assortment of inserts
GTIN (EAN)	4032248310029	
Qty.	100 pc(s).	

Type	EINSATZ A7-1 CL55	Version
Order No.	9028450000	Assortment of inserts
GTIN (EAN)	4032248310012	
Qty.	1 pc(s).	

CRIMP-SET PZ 16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Crimping tools

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 16	Version
Order No.	9012600000	Pressing tool, Crimping tool for wire-end ferrules, 6mm ² , 16mm ² ,
GTIN (EAN)	4008190035440	Indent crimp
Qty.	1 pc(s).	

Conductor nom. cross-section 10mm²

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H10,0/22 EB	Version	Packaging
Order No.	0534200000	Wire-end ferrule, Standard, 15 mm, 12 mm, Ivory	loose
GTIN (EAN)	4008190033460		
Qty.	100 pc(s).		

CRIMP-SET PZ 16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com**Accessories****Case**

- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	KOFFER PSC4-01	Version
Order No.	9028860000	Tools, Assortment box
GTIN (EAN)	4032248304608	
Qty.	1 pc(s).	

Conductor nom. cross-section 6.0mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H6,0/20 SW	Version	Packaging
Order No.	0533500000	Wire-end ferrule, Standard, 14 mm, 12 mm, black	loose
GTIN (EAN)	4008190183905		
Qty.	100 pc(s).		

CRIMP-SET PZ 16

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Conductor nom. cross-section 16mm²

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H16,0/28 GN	Version	Packaging
Order No.	0566000000	Wire-end ferrule, Standard, 21 mm, 18 mm, green	loose
GTIN (EAN)	4008190165406		
Qty.	100 pc(s).		
Type	H16,0/22 GN	Version	Packaging
Order No.	0565900000	Wire-end ferrule, Standard, 15 mm, 12 mm, green	loose
GTIN (EAN)	4008190022181		
Qty.	100 pc(s).		