

**CRIMPFIX LS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

**General ordering data**

Version	Automatic stripper and crimper
Order No.	<a href="#">9028540000</a>
Type	CRIMPFIX LS
GTIN (EAN)	4008190942687
Qty.	1 pc(s).

## CRIMPFIX LS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	330 mm	Depth (inches)	12.992 inch
Height	460 mm	Height (inches)	18.11 inch
Width	390 mm	Width (inches)	15.354 inch
Net weight	31,000 g		

## PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 - 5.5 bar	Consumables	loose cable lugs
Crimping length	6/8/10 mm	Drive	Electropneumatic
Electrical connection	100-240 V / 50/60 Hz / 110 VA	Length of wire-end ferrule	12/14/16 mm
Pulse time	approx. 1 s	Stripping range	0.5 - 2.5 mm <sup>2</sup> (~AWG 20-14)
Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>

## Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

## Important note

Product information	<b>Old Version</b> 9022650000 – SOT 1: 0.5 mm <sup>2</sup> - 1.5 mm <sup>2</sup> up to serial number CF L 1789 and CF LS 1475 9022660000 – SOT 2: 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup> up to serial number CF L 1789 and CF LS 1475 <b>New Version</b> 1440540000 – SOT 1: 0.5 mm <sup>2</sup> - 1.5 mm <sup>2</sup> from serial number CF L 1790 and CF LS 1476 1440550000 – SOT 2: 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup> from serial number CF L 1790 and CF LS 1476
---------------------	--

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads




User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## CRIMPFIX LS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## CRIMPFIX LS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Accessories / replacement parts



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

## General ordering data

Type	AIMESA CF U/LS TIN	Version
Order No.	<a href="#">1132150000</a>	Automatic machines, Replacement part
GTIN (EAN)	4032248920082	
Qty.	1 pc(s).	
Type	SOT 1 CF L/LS V3	Version
Order No.	<a href="#">1440540000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118247602	
Qty.	1 pc(s).	
Type	SCHWINGF.-OBERT.CF L	Version
Order No.	<a href="#">9022650000</a>	Automatic machines, Replacement part
GTIN (EAN)	4032248178926	
Qty.	1 pc(s).	
Type	FESA CF L/LS V1	Version
Order No.	<a href="#">1454780000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118260809	
Qty.	1 pc(s).	
Type	WTE CF L/LS V2/V3	Version
Order No.	<a href="#">1424470000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118240276	
Qty.	1 pc(s).	
Type	SOT 2 CF L/LS V4	Version
Order No.	<a href="#">1440550000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118247619	
Qty.	1 pc(s).	
Type	AIMESA CF U/L/LS SK TIN	Version
Order No.	<a href="#">1283530000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118073676	
Qty.	1 pc(s).	
Type	SCHRSA CF L/LS V1	Version
Order No.	<a href="#">1454740000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118260670	
Qty.	1 pc(s).	
Type	MAGNETSCHALTER CF L/LS	Version
Order No.	<a href="#">1523240000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118328950	
Qty.	1 pc(s).	
Type	FESA CF L/LS V2	Version
Order No.	<a href="#">1454790000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118260779	
Qty.	1 pc(s).	

Creation date April 27, 2024 8:42:41 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

**CRIMPFIX LS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

Type	CRWZG CF LS V2/V3	Version
Order No.	<a href="#">1424330000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118240146	
Qty.	1 pc(s).	
Type	SCHWINGF.-OBERT./ CFL	Version
Order No.	<a href="#">9022660000</a>	Automatic machines, Replacement part
GTIN (EAN)	4032248178940	
Qty.	1 pc(s).	
Type	EXZ-SET CF L/LS V3	Version
Order No.	<a href="#">1484880000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118293883	
Qty.	1 pc(s).	
Type	SCHRSA CF L/LS V2	Version
Order No.	<a href="#">1454750000</a>	Automatic machines, Replacement part
GTIN (EAN)	4050118260588	
Qty.	1 pc(s).	