

CRIMPSET CTI 6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: CTI 6, Stripping tool: STRIPAX, Crimping range, min.: 0.5
Order No.	9202600000
Type	CRIMPSET CTI 6
GTIN (EAN)	4032248502769
Qty.	1 pc(s).
Packaging	Plastic box

Creation date May 5, 2024 6:52:26 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

CRIMPSET CTI 6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	330 mm	Depth (inches)	12.992 inch
Height	79 mm	Height (inches)	3.11 inch
Width	413 mm	Width (inches)	16.26 inch
Net weight	4,796.62 g		

Technical data

Description of article	Set includes crimping tool for up to 6 mm ² , stripping tool and insulated connectors
------------------------	--------------------------------------------------------------------------------------------------

Assortments

Crimping range, max.	6 mm ²	Crimping range, min.	0.5 mm ²
Crimping tool	CTI 6	Number of AEH	1,900 pcs.
Packaging	Plastic box	Stripping tool	STRIPAX

Classifications

ETIM 6.0	EC000524	ETIM 7.0	EC000524
ETIM 8.0	EC000524	ETIM 9.0	EC000524
ECLASS 9.0	27-40-02-18	ECLASS 9.1	27-40-02-18
ECLASS 10.0	27-40-02-18	ECLASS 11.0	27-40-02-18
ECLASS 12.0	27-40-02-18	ECLASS 13.0	27-40-02-18

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

CRIMPSET CTI 6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Crimping tools



Crimping tools for insulated connectors

cable lugs, terminal pins, parallel and serial connectors, plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

General ordering data

Type	CTI 6	Version
Order No.	9006120000	Pressing tool, Crimping tool for contacts, 0.5mm², 6mm², Oval
GTIN (EAN)	4008190044527	crimping, Double crimp
Qty.	1 pc(s).	

Pin cable lugs



Insulated pin-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIP 2,5R12 V	Version
Order No.	9200470000	cable lug, terminal end, Insulated cable connector, 1.5 mm² - 2.5 mm², blue
GTIN (EAN)	4032248410316	
Qty.	100 pc(s).	
Type	LIP 1,5R12 V	Version
Order No.	9200460000	cable lug, terminal end, Insulated cable connector, 0.5 mm² - 1.5 mm², red
GTIN (EAN)	4032248410309	
Qty.	100 pc(s).	
Type	LIP 6R14 V	Version
Order No.	9200480000	cable lug, terminal end, Insulated cable connector, 4 mm² - 6 mm², yellow
GTIN (EAN)	4032248410323	
Qty.	100 pc(s).	

CRIMPSET CTI 6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version
Order No.	9005000000	Tools, Stripping and cutting tool
GTIN (EAN)	4008190072506	
Qty.	1 pc(s).	

Cable-lug sleeves



Insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIF 2,5F638 R	Version
Order No.	9200560000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	40322484 10408	2.5 mm ²
Qty.	100 pc(s).	
Type	LIF 1,5F638 R	Version
Order No.	9200540000	cable lug, terminal end, Insulated cable connector, 1.5 mm ² , 0.5 mm ² -
GTIN (EAN)	40322484 10385	1.5 mm ²
Qty.	100 pc(s).	
Type	LIF 6F638 R	Version
Order No.	9200570000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	40322484 10415	mm ²
Qty.	100 pc(s).	

CRIMPSET CTI 6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	LIF 1,5F288 R	Version
Order No.	9200520000	cable lug, terminal end, Insulated cable connector, 1.5 mm ² , 0.5 mm ² -
GTIN (EAN)	4032248410361	1.5 mm ²
Qty.	100 pc(s).	

Forked cable lugs



Insulated forked-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIS 6M6 V	Version
Order No.	9200430000	cable lug, terminal end, Insulated cable connector, 4 mm ² - 6
GTIN (EAN)	4032248410279	mm ² , yellow
Qty.	100 pc(s).	
Type	LIS 2,5M5 V	Version
Order No.	9200380000	cable lug, terminal end, Insulated cable connector, 1.5 mm ² - 2.5
GTIN (EAN)	4032248410224	mm ² , blue
Qty.	100 pc(s).	
Type	LIS 1,5M4 V	Version
Order No.	9200310000	cable lug, terminal end, Insulated cable connector, 0.5 mm ² - 1.5
GTIN (EAN)	4032248410132	mm ² , red
Qty.	100 pc(s).	

Ring cable lugs



Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIR 2,5M6 V	Version
Order No.	9200190000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4032248410019	2.5 mm ²
Qty.	100 pc(s).	
Type	LIR 6M5 V	Version
Order No.	9200240000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4032248410064	mm ²
Qty.	100 pc(s).	

Creation date May 5, 2024 6:52:26 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

CRIMPSET CTI 6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	LIR 1,5M4 V	Version
Order No.	9200090000	cable lug, terminal end, Insulated cable connector, 1.5 mm ² , 0.5 mm ² -
GTIN (EAN)	4032248409853	1.5 mm ²
Qty.	100 pc(s).	
Type	LIR 1,5M5 V	Version
Order No.	9200100000	cable lug, terminal end, Insulated cable connector, 1.5 mm ² , 0.5 mm ² -
GTIN (EAN)	4032248409860	1.5 mm ²
Qty.	100 pc(s).	
Type	LIR 2,5M5 V	Version
Order No.	9200180000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4032248409808	2.5 mm ²
Qty.	100 pc(s).	
Type	LIR 6M6 V	Version
Order No.	9200250000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4032248410071	mm ²
Qty.	100 pc(s).	

Inserts



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	EINSATZ BA8-PSC 80	Version
Order No.	9202310000	Assortment of inserts
GTIN (EAN)	4032248486687	
Qty.	1 pc(s).	

Joint connector



Fully-insulated joint connector made from PVC or PC/PA

- Conventional designs
- Not soldered

General ordering data

Type	LIB 2,5B25 VF	Version
Order No.	9200500000	cable lug, terminal end, Insulated cable connector, 1.5 mm ² - 2.5
GTIN (EAN)	4032248410347	mm ² , blue
Qty.	100 pc(s).	

Creation date May 5, 2024 6:52:26 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

CRIMPSET CTI 6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	LIB 6B26 VF	Version
Order No.	9200510000	cable lug, terminal end, Insulated cable connector, 4 mm² - 6
GTIN (EAN)	4032248410354	mm², yellow
Qty.	100 pc(s).	
Type	LIB 1,5B25 VF	Version
Order No.	9200490000	cable lug, terminal end, Insulated cable connector, 0.5 mm² - 1.5
GTIN (EAN)	4032248410330	mm², red
Qty.	100 pc(s).	

Case



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	KOFFER PSC80 PC	Version
Order No.	9202330000	Tools, Empty box / Case
GTIN (EAN)	4032248486700	
Qty.	1 pc(s).	