

**CRIMP-SET KONTAKTE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Crimp sets

**General ordering data**

Version	Assortment box, Colour code: DIN
Order No.	<a href="#">9202640000</a>
Type	CRIMP-SET KONTAKTE
GTIN (EAN)	4032248503322
Qty.	1 pc(s).

**CRIMP-SET KONTAKTE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	330 mm	Depth (inches)	12.992 inch
Height	57 mm	Height (inches)	2.244 inch
Width	413 mm	Width (inches)	16.26 inch
Net weight	3,503 g		

**Technical data**

Description of article	Crimp set contacts with insulated connectors and wire-end ferrules with plastic collars
------------------------	---

**Assortments**

Colour code	DIN	Number of AEH	2,000 pcs.
-------------	-----	---------------	------------

**Classifications**

ETIM 6.0	EC000524	ETIM 7.0	EC000524
ETIM 8.0	EC000524	ETIM 9.0	EC000524
ECLASS 9.0	27-40-02-18	ECLASS 9.1	27-40-02-18
ECLASS 10.0	27-40-02-18	ECLASS 11.0	27-40-02-18
ECLASS 12.0	27-40-02-18	ECLASS 13.0	27-40-02-18

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**CRIMP-SET KONTAKTE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****packed loose in polythene bag**

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

**General ordering data**

Type	H0,5/14D W	Version		Packaging	
Order No.	<a href="#">9019010000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white		loose	
GTIN (EAN)	4008190120931				
Qty.	500 pc(s).				

**packed loose in polythene bag**

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

**General ordering data**

Type	H1,0/14D R	Version		Packaging	
Order No.	<a href="#">9019080000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red		loose	
GTIN (EAN)	4008190090623				
Qty.	500 pc(s).				

## CRIMP-SET KONTAKTE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Inserts



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

## General ordering data

Type	EINSATZ A8-1 CL55	Version
Order No.	<a href="#">9028460000</a>	Assortment of inserts
GTIN (EAN)	4032248310029	
Qty.	100 pc(s).	
Type	EINSATZ A7-1 CL55	Version
Order No.	<a href="#">9028450000</a>	Assortment of inserts
GTIN (EAN)	4032248310012	
Qty.	1 pc(s).	

## Case



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

## General ordering data

Type	KOFFER CARRY LITE 55	Version
Order No.	<a href="#">9202000000</a>	Tools, Empty box / Case
GTIN (EAN)	4032248481231	
Qty.	1 pc(s).	

**CRIMP-SET KONTAKTE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****packed loose in polythene bag**

- supplied loose in polybag
- DIN colour code
- other colour code

**General ordering data**

Type	H2,5/15D BL	Version		Packaging	
Order No.	<a href="#">9019160000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, blue		loose	
GTIN (EAN)	4008190028732				
Qty.	500 pc(s).				

**packed loose in polythene bag**

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

Type	H0,75/14D GR	Version		Packaging	
Order No.	<a href="#">9019040000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, grey		loose	
GTIN (EAN)	4008190099077				
Qty.	500 pc(s).				

## CRIMP-SET KONTAKTE

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Conductor nom. cross-section 6.0mm<sup>2</sup>

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

## General ordering data

Type	H6,0/20D GE	Version	Packaging
Order No.	<a href="#">9019220000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, yellow	loose
GTIN (EAN)	4008190151607		
Qty.	100 pc(s).		

## Joint connector



## Fully-insulated joint connector made from PVC or PC/PA

- Conventional designs
- Not soldered

## General ordering data

Type	LIB 6B26 VF	Version
Order No.	<a href="#">9200510000</a>	cable lug, terminal end, Insulated cable connector, 4 mm <sup>2</sup> - 6 mm <sup>2</sup> , yellow
GTIN (EAN)	4032248410354	
Qty.	100 pc(s).	
Type	LIB 2,5B25 VF	Version
Order No.	<a href="#">9200500000</a>	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup> , blue
GTIN (EAN)	4032248410347	
Qty.	100 pc(s).	
Type	LIB 1,5B25 VF	Version
Order No.	<a href="#">9200490000</a>	cable lug, terminal end, Insulated cable connector, 0.5 mm <sup>2</sup> - 1.5 mm <sup>2</sup> , red
GTIN (EAN)	4032248410330	
Qty.	100 pc(s).	

## CRIMP-SET KONTAKTE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## packed loose in polythene bag



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

## General ordering data

Type	H1,5/14D SW	Version	Packaging
Order No.	<a href="#">9019120000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, black	loose
GTIN (EAN)	4008190153793		
Qty.	500 pc(s).		

## Ring cable lugs



## Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

## General ordering data

Type	LIR 6M6 V	Version
Order No.	<a href="#">9200250000</a>	cable lug, terminal end, Insulated cable connector, 6 mm <sup>2</sup> , 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4032248410071	
Qty.	100 pc(s).	
Type	LIR 2,5M5 V	Version
Order No.	<a href="#">9200180000</a>	cable lug, terminal end, Insulated cable connector, 2,5 mm <sup>2</sup> , 1,5 mm <sup>2</sup> - 2,5 mm <sup>2</sup>
GTIN (EAN)	4032248409808	
Qty.	100 pc(s).	
Type	LIR 1,5M4 V	Version
Order No.	<a href="#">9200090000</a>	cable lug, terminal end, Insulated cable connector, 1,5 mm <sup>2</sup> , 0,5 mm <sup>2</sup> - 1,5 mm <sup>2</sup>
GTIN (EAN)	4032248409853	
Qty.	100 pc(s).	
Type	LIR 1,5M5 V	Version
Order No.	<a href="#">9200100000</a>	cable lug, terminal end, Insulated cable connector, 1,5 mm <sup>2</sup> , 0,5 mm <sup>2</sup> - 1,5 mm <sup>2</sup>
GTIN (EAN)	4032248409860	
Qty.	100 pc(s).	

## CRIMP-SET KONTAKTE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Pin cable lugs

**Insulated pin-cable connector made from PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel

## General ordering data

Type	LIP 6R14 V	Version
Order No.	<a href="#">9200480000</a>	cable lug, terminal end, Insulated cable connector, 4 mm <sup>2</sup> - 6 mm <sup>2</sup> , yellow
GTIN (EAN)	40322484 10323	
Qty.	100 pc(s).	
Type	LIP 1,5R12 V	Version
Order No.	<a href="#">9200460000</a>	cable lug, terminal end, Insulated cable connector, 0.5 mm <sup>2</sup> - 1.5 mm <sup>2</sup> , red
GTIN (EAN)	40322484 10309	
Qty.	100 pc(s).	
Type	LIP 2,5R12 V	Version
Order No.	<a href="#">9200470000</a>	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup> , blue
GTIN (EAN)	40322484 10316	
Qty.	100 pc(s).	

## packed loose in polythene bag



- supplied loose in polybag
- DIN colour code
- other colour code

## General ordering data

Type	H4,0/18D GR	Version	Packaging
Order No.	<a href="#">9019190000</a>	Wire-end ferrule, Standard, 12 mm, 10 mm, grey	loose
GTIN (EAN)	4008190141349		
Qty.	500 pc(s).		



## CRIMP-SET KONTAKTE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Cable-lug sleeves


**Insulated tab-connector sleeves made from PVC with copper sleeve**

- Commercially available designs
- Not soldered
- With conical entry funnel

## General ordering data

Type	LIF 1,5F638 R	Version
Order No.	<a href="#">9200540000</a>	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> , 0.5 mm <sup>2</sup> -
GTIN (EAN)	40322484 10385	1.5 mm <sup>2</sup>
Qty.	100 pc(s).	
Type	LIF 6F638 R	Version
Order No.	<a href="#">9200570000</a>	cable lug, terminal end, Insulated cable connector, 6 mm <sup>2</sup> , 4 mm <sup>2</sup> - 6
GTIN (EAN)	40322484 10415	mm <sup>2</sup>
Qty.	100 pc(s).	
Type	LIF 2,5F638 R	Version
Order No.	<a href="#">9200560000</a>	cable lug, terminal end, Insulated cable connector, 2.5 mm <sup>2</sup> , 1.5 mm <sup>2</sup> -
GTIN (EAN)	40322484 10408	2.5 mm <sup>2</sup>
Qty.	100 pc(s).	
Type	LIF 1,5F288 R	Version
Order No.	<a href="#">9200520000</a>	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> , 0.5 mm <sup>2</sup> -
GTIN (EAN)	40322484 10361	1.5 mm <sup>2</sup>
Qty.	100 pc(s).	