

THERMOMETER 610 LC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The 610 LC infrared thermometer allows you to gauge the surface temperature precisely - quickly and safely, with no contact.

- Contactless measurement of temperatures from -20°C to +260°C
- Resolution: 1°C
- Measuring rate: 2.5 times per second
- Laser spot marking of measuring point
- Backlit display
- Including battery status indicator
- Automatic switch-off
- Including protective pouch

General ordering data

Version	Testing tools, Infrared thermometer
Order No.	9427520000
Type	THERMOMETER 610 LC
GTIN (EAN)	4032248407033
Qty.	1 pc(s).
Delivery status	Discontinued
Available until	2023-05-01

THERMOMETER 610 LC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	40 mm	Depth (inches)	1.575 inch
Height	44 mm	Height (inches)	1.732 inch
Width	170 mm	Width (inches)	6.693 inch
Net weight	297 g		

Technical data

Description of article	Infrared thermometer
------------------------	----------------------

Measuring and testing devices

Battery type	1.5 V type AAA battery	Display	digital
Measured temperature value, max.	260 °C	Measured temperature value, min.	-20 °C
Working temperature, max.	50 °C	Working temperature, min.	0 °C

Classifications

ETIM 6.0	EC000601	ETIM 7.0	EC000601
ETIM 8.0	EC000601	ECLASS 9.0	27-20-11-20
ECLASS 9.1	27-20-02-90	ECLASS 10.0	27-20-11-20
ECLASS 11.0	27-20-11-20	ECLASS 12.0	27-20-11-20
ECLASS 13.0	27-20-11-20		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

THERMOMETER 610 LC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



THERMOMETER 610 LC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories**

Accessories for testing and measuring equipment

**General ordering data**

Type	BATTERIE 1,5V MICRO	Version
Order No.	9201310000	Testing tools, Battery
GTIN (EAN)	4032248421121	
Qty.	2 pc(s).	