

**SIHA 1/G20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

**General ordering data**

Version	Fuse holder for feed-through modular terminal, pluggable
Order No.	<a href="#">9537550000</a>
Type	SIHA 1/G20
GTIN (EAN)	4008190118686
Qty.	25 pc(s).

## SIHA 1/G20

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	43.93 mm	Depth (inches)	1.73 inch
Height	33.38 mm	Height (inches)	1.314 inch
Width	5.95 mm	Width (inches)	0.234 inch
Net weight	6.43 g		

## Temperatures

Operating temperature	-50 °C...120	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

## Material data

Material	Wemid	Insulating material	Wemid
Colour	dark beige	UL 94 flammability rating	V-0

## System specifications

Version	Fuse cartridge	End cover plate required	No
---------	----------------	--------------------------	----

## Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

## Conductors for clamping (rated connection)

Type of connection	Plug-in connection
--------------------	--------------------

## General

Installation advice	Direct mounting	Operating temperature range, max.	120 °C
---------------------	-----------------	-----------------------------------	--------

## Rating data

Rated voltage	250 V	Rated current	6.3 A
Rated impulse withstand voltage	4 kV	Pollution severity	3

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

## Approvals

ROHS	Conform
------	---------

### SIHA 1/G20

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Con-  
formity

[Confirmation of Standards EN 45545-2\\_2020-10](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[Beipackzettel\\_SIHA3.pdf](#)

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

### SIHA 1/G20

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

