

**SIHA 1/G20 10-36V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

**General ordering data**

Version	Fuse holder for feed-through modular terminal, pluggable
Order No.	<a href="#">9537560000</a>
Type	SIHA 1/G20 10-36V
GTIN (EAN)	4008190125066
Qty.	25 pc(s).

## SIHA 1/G20 10-36V

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	43.93 mm	Depth (inches)	1.73 inch
Height	33.38 mm	Height (inches)	1.314 inch
Width	5.95 mm	Width (inches)	0.234 inch
Net weight	8.32 g		

## Temperatures

Operating temperature	-50 °C...120	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

## Material data

Material	Wemid	Insulating material	Wemid
Colour	dark beige	UL 94 flammability rating	V-0

## System specifications

Version	Fuse cartridge	End cover plate required	No
---------	----------------	--------------------------	----

## Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

## Conductors for clamping (rated connection)

Type of connection	Plug-in connection
--------------------	--------------------

## General

Installation advice	Direct mounting	Operating temperature range, max.	120 °C
---------------------	-----------------	-----------------------------------	--------

## Rating data

Rated voltage	250 V	Rated current	6.3 A
Rated impulse withstand voltage	4 kV	Pollution severity	3

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## SIHA 1/G20 10-36V

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

