

**ZEW 35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

**General ordering data**

|            |  |
|------------|--|
| Version    | End bracket, Wemid, dark beige, Rail: TS 35, Snap-on |
| Order No.  | <a href="#">9540000000</a>                           |
| Type       | ZEW 35   |
| GTIN (EAN) | 4008190956264  |
| Qty.       | 20 pc(s).  |

## ZEW 35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 40 mm   | Depth (inches)  | 1.575 inch |
| Height     | 55 mm   | Height (inches) | 2.165 inch |
| Width      | 6 mm    | Width (inches)  | 0.236 inch |
| Net weight | 6.688 g |                 |            |

## Temperatures

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |
|----------------------------------|--------|----------------------------------|--------|

## Material data

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-2   |        |            |

## System specifications

|         |                   |      |       |
|---------|-------------------|------|-------|
| Version | For the terminals | Rail | TS 35 |
|---------|-------------------|------|-------|

## Additional technical data

|                     |                 |           |           |
|---------------------|-----------------|-----------|-----------|
| Installation advice | Direct mounting | Interlock | screwless |
| Type of mounting    | Snap-on         |           |           |

## Dimensions

|              |       |
|--------------|-------|
| TS 35 offset | 41 mm |
|--------------|-------|

## General

|                     |                 |      |       |
|---------------------|-----------------|------|-------|
| Installation advice | Direct mounting | Rail | TS 35 |
|---------------------|-----------------|------|-------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001041    | ETIM 7.0    | EC001041    |
| ETIM 8.0    | EC001041    | ETIM 9.0    | EC001041    |
| ECLASS 9.0  | 27-14-11-35 | ECLASS 9.1  | 27-14-11-35 |
| ECLASS 10.0 | 27-14-11-35 | ECLASS 11.0 | 27-14-11-35 |
| ECLASS 12.0 | 27-14-11-35 | ECLASS 13.0 | 27-25-03-02 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">CAD data – STEP</a>                          |
| Engineering Data            | <a href="#">Zuken E3.S</a>                               |
| Product Change Notification | <a href="#">20210823 Technical Change ZEW 15, ZEW 35</a> |
| User Documentation          | <a href="#">StorageConditionsTerminalBlocks</a>          |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                 |
| Brochures                   |  |

## ZEW 35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Accessories



## System accessory

Discover a wide range of accessories for your u-remote system - the ideal addition to make your applications even more efficient and flexible.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | EM 8/30                    | Version   |
| Order No.  | <a href="#">1806120000</a> | EM, Terminal marker, 32.4 x 7.2 mm, Pitch in mm (P): 7.20 |
| GTIN (EAN) | 4032248275298              | Weidmueller, Transparent                                  |
| Qty.       | 50 pc(s).                  |   |

## Blank



The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers.

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | WAD 5 MC NE WS             | Version   |
| Order No.  | <a href="#">1112910000</a> | Group markers, Cover, 33.3 x 5 mm, Pitch in mm (P): 5.00 WDU 2.5, |
| GTIN (EAN) | 4032248891689              | WEW 35/2, ZEW 35/2, white   |
| Qty.       | 48 pc(s).                  |   |
| Type       | WAD 5 MC NE GE             | Version   |
| Order No.  | <a href="#">1112920000</a> | Group markers, Cover, 33.3 x 5 mm, Pitch in mm (P): 5.00 WDU 2.5, |
| GTIN (EAN) | 4032248891771              | WEW 35/2, ZEW 35/2, yellow  |
| Qty.       | 48 pc(s).                  |   |

## ZEW 35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/5 MC NE WS           | Version   |
| Order No.  | <a href="#">1609801044</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111              | Weidmueller, white  |
| Qty.       | 1,000 pc(s).               |   |

## ZGB pivotable group tag holder



The ZGB 15 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 15.

The ZGB 30 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 7.

Inlay tags and protective strips can be found under "Accessories".

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZGB 30                     | Version   |
| Order No.  | <a href="#">1611930000</a> | Terminal markers, Terminal marker, 32 x 7 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190002251              | Weidmueller, white  |
| Qty.       | 20 pc(s).                  |   |

  

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZGB 15                     | Version   |
| Order No.  | <a href="#">1636530000</a> | Terminal markers, Terminal marker, 15 x 7 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190297053              | Weidmueller, white  |
| Qty.       | 20 pc(s).                  |   |