

DMS MANUELL 0,5-1,7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

| | |
|------------|----------------------------|
| Version | Torque screwdriver |
| Order No. | 9918370000 |
| Type | DMS MANUELL 0,5-1,7 |
| GTIN (EAN) | 4032248388332 |
| Qty. | 1 pc(s). |

DMS MANUELL 0,5-1,7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|----------------|------------|
| Width | 200 mm | Width (inches) | 7.874 inch |
| Net weight | 166.1 g | | |

Technical data

| | |
|------------------------|--|
| Description of article | Torque screwdriver, from 0.5-1.7 Nm |
|------------------------|--|

Screwing tools

| | | | |
|----------------------|--------|----------------------|--------|
| Torque setting, max. | 1.7 Nm | Torque setting, min. | 0.5 Nm |
|----------------------|--------|----------------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000149 | ETIM 7.0 | EC000149 |
| ETIM 8.0 | EC000149 | ETIM 9.0 | EC000149 |
| ECLASS 9.0 | 21-04-04-07 | ECLASS 9.1 | 21-04-04-90 |
| ECLASS 10.0 | 21-04-50-03 | ECLASS 11.0 | 21-04-50-03 |
| ECLASS 12.0 | 21-04-50-03 | ECLASS 13.0 | 21-04-50-03 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 8a39b146-a7e9-4fe1-a2bc-f82c0bb3aeeb |

Downloads

| | |
|-----------------------------|---|
| Product Change Notification | Produktänderungsmitteilung Product Change Notification |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

DMS MANUELL 0,5-1,7

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

... slotted-head screws

Interchangeable bits for torque screwdriver

Drive output acc. to DIN 5264, ISO 2380/1



General ordering data

| | | |
|------------|----------------------------|--------------------|
| Type | WK S 0,6X3,5 | Version |
| Order No. | 9918540000 | Screwdriver insert |
| GTIN (EAN) | 4032248388905 | |
| Qty. | 1 pc(s). | |
| Type | WK S 0,8X4,0 | Version |
| Order No. | 9918550000 | Screwdriver insert |
| GTIN (EAN) | 4032248388912 | |
| Qty. | 1 pc(s). | |
| Type | WK S 0,4X2,5 | Version |
| Order No. | 9918520000 | Screwdriver insert |
| GTIN (EAN) | 4032248388882 | |
| Qty. | 1 pc(s). | |
| Type | WK S 0,5X3,0 | Version |
| Order No. | 9918530000 | Screwdriver insert |
| GTIN (EAN) | 4032248388899 | |
| Qty. | 1 pc(s). | |
| Type | WK S 1,0X5,5 | Version |
| Order No. | 9918560000 | Screwdriver insert |
| GTIN (EAN) | 4032248388936 | |
| Qty. | 1 pc(s). | |

... Phillips crosshead

Interchangeable bits for torque screwdriver

Drive output acc. to DIN 5260-PH, ISO 8764/1-PH



General ordering data

| | | |
|------------|----------------------------|--------------------|
| Type | WK K PH0 | Version |
| Order No. | 9918570000 | Screwdriver insert |
| GTIN (EAN) | 4032248388943 | |
| Qty. | 1 pc(s). | |

DMS MANUELL 0,5-1,7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

| | | |
|------------|----------------------------|--------------------|
| Type | WK K PH1 | Version |
| Order No. | 9918580000 | Screwdriver insert |
| GTIN (EAN) | 4032248388950 | |
| Qty. | 1 pc(s). | |

| | | |
|------------|----------------------------|--------------------|
| Type | WK K PH2 | Version |
| Order No. | 9918590000 | Screwdriver insert |
| GTIN (EAN) | 4032248388967 | |
| Qty. | 1 pc(s). | |

... Pozidriv crosshead**Interchangeable bits for torque screwdriver**

Drive output acc. to DIN 5260-PZ, ISO 8764/1-PZ

**General ordering data**

| | | |
|------------|----------------------------|--------------------|
| Type | WK K PZ2 | Version |
| Order No. | 9918620000 | Screwdriver insert |
| GTIN (EAN) | 4032248388998 | |
| Qty. | 1 pc(s). | |

| | | |
|------------|----------------------------|--------------------|
| Type | WK K PZ1 | Version |
| Order No. | 9918610000 | Screwdriver insert |
| GTIN (EAN) | 4032248388981 | |
| Qty. | 1 pc(s). | |

| | | |
|------------|----------------------------|--------------------|
| Type | WK K PZ0 | Version |
| Order No. | 9918600000 | Screwdriver insert |
| GTIN (EAN) | 4032248388974 | |
| Qty. | 1 pc(s). | |