

**WK S 0,6X3,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Interchangeable bits for torque screwdriver**

Drive output acc. to DIN 5264, ISO 2380/1

**General ordering data**

Version	Screwdriver insert
Order No.	<a href="#">9918540000</a>
Type	WK S 0,6X3,5
GTIN (EAN)	4032248388905
Qty.	1 pc(s).

**WK S 0,6X3,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	4 mm	Depth (inches)	0.157 inch
Height	4 mm	Height (inches)	0.157 inch
Width	175 mm	Width (inches)	6.89 inch
Net weight	22 g		

**Technical data**

Description of article	Interchangeable bit for slotted screws, size 0.6x3.5
------------------------	--

**Screwing tools**

Blade length	175 mm	Blade thickness (A)	0.6 mm
Blade width (B)	3.5 mm	Form	Slotted
Torque setting, max.	1.1 Nm		

**Classifications**

ETIM 6.0	EC002116	ETIM 7.0	EC002116
ETIM 8.0	EC003864	ETIM 9.0	EC003864
ECLASS 9.1	21-04-04-90	ECLASS 10.0	21-04-04-90
ECLASS 11.0	21-04-42-04	ECLASS 12.0	21-04-42-04
ECLASS 13.0	21-04-42-04		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	6a3438d7-aa8c-48e4-8879-adf736ca79e3

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**WK S 0,6X3,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Torque screwdriver**

If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

**General ordering data**

Type	DMS MANUELL 0,5-1,7	Version
Order No.	<a href="#">9918370000</a>	Torque screwdriver
GTIN (EAN)	4032248388332	
Qty.	1 pc(s).	
Type	DMS MANUELL 2,0-7,0	Version
Order No.	<a href="#">9918380000</a>	Torque screwdriver
GTIN (EAN)	4032248388349	
Qty.	1 pc(s).	