IE-SW-BL08-6TX-2ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



- Variations with 5 or 8 ports
- Variations for Gigabit Ethernet
- Sturdy metal housing
- Compact design
- Two redundant power inputs 12/24/48 V DC
- Variations with copper and fibre-optic interface (multi-mode and singlemode)
- Extensive approvals: CE, FCC, cULus, Class I Div. 2 / ATEX Zone 2, DNV-GL

General ordering data

Version	Network switch, unmanaged, Fast Ethernet, Number of ports: 6x RJ45, 2 * ST Multi-mode, IP30, -10 °C...60 °C
Order No.	1240930000
Type	IE-SW-BL08-6TX-2ST
GTIN (EAN)	4050118028744
Qty.	1 pc(s).

Creation date March 28, 2024 10:14:20 AM CET

IE-SW-BL08-6TX-2ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	115 mm	Height (inches)	4.528 inch
Width	50 mm	Width (inches)	1.969 inch
Net weight	275 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-10 °C...60 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	EN 55032, EN 55035, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz - 6 GHz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 2 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 1 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8 PFMF: 100A/m	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA IIC T4 Gc
Free fall	According to IEC 60068-2-32	Safety standard	UL508
Ship use	DNV	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	-10 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	100 Mbps	
Transceiver type	Multimode	
Connector type	ST-Duplex	
Transmission distance, typ.	5 km	
Wavelength	typ.	1,300 nm
	Wavelength	TX
	min.	1,260 nm
	max.	1,360 nm
	Wavelength	RX
	min.	1,100 nm
	max.	1,600 nm
Receive power	min.	-32 dBm
	max.	-3 dBm
Transmission power	min.	-20 dBm
	max.	-10 dBm

IE-SW-BL08-6TX-2ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Link-budget	12 dB

Guarantee

Time interval	5 years

Interfaces

Fibre-optic ports	100BaseFX ports (ST connector), Multimode	Function DIP switch	1x for enabling/disabling the broadcast storm protection
LED indicator	PWR1, PWR2, 10/100M (TP-Port), 100M (fibre-optic port).	Number of ports	6x RJ45, 2 * ST Multi-mode
RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port		

MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	2,428,212 h

Power supply

Connection type	1 removable 4-pin terminal block	
Current consumption	0.22 A at 24 V	
Overload current protection	1.1 A	
Reverse polarity protection	Available	
Voltage supply	12/24/48 V DC, 2 redundant inputs	
Voltage supply range	Voltage type	DC
	Voltage, min.	9.6 V
	Voltage, max.	60 V

Switch characteristics

Bandwidth backplane	1.6 Gbit/s	MAC table size	2 K
Packet buffer size	768 Kbit		

Technical data

Housing main material	Aluminium	Protection degree	IP30
Speed	Fast Ethernet	Switch	unmanaged
Type of mounting	DIN rail		

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3x for flow control		

IE-SW-BL08-6TX-2ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ETIM 9.0	EC000734
ECLASS 9.0	19-17-01-06	ECLASS 9.1	19-17-01-06
ECLASS 10.0	19-17-04-02	ECLASS 11.0	19-17-04-02
ECLASS 12.0	19-17-04-02	ECLASS 13.0	19-17-04-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197
Certificate no. (cULusEX)	E223527

Downloads

Approval/Certificate/Document of Conformity	DNV certificate ATEX certificate KC certificate EU Declaration of Conformity UK Declaration of Conformity
Engineering Data	CAD data – STEP
Product Change Notification	Product Change Notification IE-SW-BL08-series
User Documentation	Hardware Installation Guide
Catalogues	Catalogues in PDF-format

IE-SW-BL08-6TX-2ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ethernet



- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

General ordering data

Type	VDATA CAT6	Version
Order No.	1348590000	Terminal rail fixing, Surge protection, Cat.6, PoE, 802.3 bt at Type 1,
GTIN (EAN)	4050118153002	802.3 bt at Type 2, 802.3 bt at Type 3, 802.3 bt at Type 4
Qty.	1 pc(s).	

Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks



General ordering data

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	

IE-SW-BL08-6TX-2ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

ST



Mounting rail outlet, ST junction design according to IEC 61754-2

General ordering data

Type	IE-XM-ST/ST	Version
Order No.	8808340000	Mounting rail outlet, fibre-optic, ST-ST coupler, IP20
GTIN (EAN)	4032248505920	
Qty.	1 pc(s).	